


MatrixPRO-II 3G/HD/SD-SDI series

High-speed 3G serial digital routers



- **Three cost-effective, compact models available**
- **Genlock input with loop through**
- **Flexible control**

Barco's MatrixPRO-II SD/HD/3G-SDI series offers three models of high-speed serial routers: 8x8, 16x16 and 32x32. All three models are compact, have an extremely slim profile, are cost-effective, and provide an excellent solution for applications where budget and space are at premium.

Featuring genlock input

All routers support SDI formats from SD formats to 3G/HD. Their superior design allows for image switching and signal distribution without artifacts. They all feature a genlock input with loop through, ensuring that all switching is synchronized with the house sync.

Flexible control

The routers can be controlled from the front panel, RS-232, Ethernet connections or the Encore and ScreenPRO-II presentation systems. Barco's MatrixPRO-II SDI router series allows a single unit to be subdivided into multiple layers.

PRODUCT SPECIFICATIONS**MATRIXPRO-II 3G/HD/SD-SDI SERIES**

| | |
|--------------------------|---|
| Supported signal formats | DVB-ASI, SMPTE 259M, SMPTE 292M, SMPTE 424M; 270M bps – 2.97Gbps; 2K, 2048x1556/23.98 and 24 |
| Inputs | <ul style="list-style-type: none">Standard: SMPTE 259M / SMPTE 292M / SMPTE 424MData rate: 270Mbps – 1.485Gbps / 2.97GbpsConnector: 75 ohm BNC femaleImpedance: 75 ohm nominalReturn loss: > 15dB (5MHz-1.485Ghz); > 10dB (1.5GHz – 3GHz)Cable equalization:<ul style="list-style-type: none">Automatic up to 70m @ 2.97Gbps, typical Belden 1694AAutomatic up to 100m @ 1.485Gbps, typical Belden 1694AAutomatic up to 300m @ 270Mbps, typical Belden 8281 |
| Outputs | <ul style="list-style-type: none">Connector: 75 ohm BNC femaleImpedance: 75 ohm nominalReturn loss: > 15dB (5MHz-1.485Ghz); > 10dB (1.5GHz – 3GHz)Signal level: 800mVp-p \pm10%Rise/fall time:<ul style="list-style-type: none">- 20% - 80%- SD limit: 0.4ns – 1.5ns, < 0.5ns rise/fall variation;- HD limit: < 270ps, < 100ps rise/fall variation;- 3G-HD limit: < 135ps, < 50ps rise/fall variationAmplitude overshoot: < 10%Signal polarity: Non-inverting electrical with respect to inputs |
| Signal Speed | <ul style="list-style-type: none">Timing jitter: SD: < 0.2 UI; 3G-HD/HD: <1UIAlignment jitter: SD: <0.2UI; 3G-HD/HD: <0.2UI |
| Safety Regulations | Compliant with CE EN55103-1 and 2 |
| Control | Serial port: RS-232, DB9 connector female Ethernet port: 10/100BaseT Ethernet bus, 1x RJ45 connector |
| Power consumption | <ul style="list-style-type: none">R9004661 (8x8): current: @ +15V/-15V: 900/2 mA - power: 14WR9004661 (16x16): current: @ +15V/-15V: 1,273/4 mA - power: 19WR9004662 (32x32): current: @ +15V/-15V: 1,302/1,035 mA - power: 35W |
| Power supply (R9871081) | <ul style="list-style-type: none">AC supply: 100-240 VAC, 50-60 Hz / Max. 1.6AAC main connector: IEC 320DC output: current: +15V, max 2.2A / -15V, max 1.35A / Power: maximum 43WDC connector: DB9, femaleWeight: 0.35 kg / 0.77 lbsSafety standards: compliant with CE EN60950, UL-1950/CSA22.2 |
| Dimensions (HxWxD) | <ul style="list-style-type: none">R9004661 (8x8) - R9004660 (16x16): 44 x 483 x 50 mm / 1.73" x 19" x 1.97"R9004662 (32x32): 88 x 483 x 50 mm / 3.46" x 19" x 1.97" |
| Weight | <ul style="list-style-type: none">R9004661 (8x8): 1.3 kg / 2.86 lbsR9004660 (16x16): 1.4kg / 3.08 lbsR9004662 (32x32): 2.2 kg / 4.84 lbs |

Last updated: 26 Nov 2019

Technical specifications are subject to change without prior notice. Please check www.barco.com for the latest information.