

FLDX 1.2 - 1.7 : 1 (EN63)

WUXGA 1.12-1.58:1

WQXGA/4K 1.20-1.70:1

F80: 1.59 - 2.24 : 1 (WQXGA/4K UHD)



PRODUCT SPECIFICATIONS**FLDX 1.2 - 1.7 : 1 (EN63)**

Platforms	For F35, FL40, F70, F80* and F90 projector series *requires lens adapter R98014421. F80 specific throw ratio: 1.59 -2.24 : 1 (WQXGA/4K UHD)
Working F/#	F 2.4-2.7 Motorized Iris F# 2.4-6.5 with memory
Zoom ratio	1.42 Motorized zoom and focus with memory
Focal length	23.95-34.02 mm
Focus Range	Standard: 1.5m – 15m
Weight	2.8 kg
Shipping weight	3.4 kg
Throw Ratio	DMD chip WUXGA 1.12-1.58 :1 WQXGA 1.20-1.70:1 Image size tolerance +/-2%

Last updated: 24 Feb 2021

Technical specifications are subject to change without prior notice. Please check www.barco.com for the latest information.