

ClickShare CX-30

Seamless wireless conferencing for small to medium-sized meeting and conference rooms



- Full BYOD support
- Remote collaboration with Button or Desktop App
- Works with your device, conferencing platform & a wide range of AV peripherals
- Enhanced security, connected and cloud managed
- Full interactivity

For better hybrid meetings, participants need to feel engaged and inspired. ClickShare CX-30 from Barco offers a seamless one-click wireless conferencing room system to bring teams together – wherever they are. Compatible with any PC, laptop or Mac device running Windows, Android or iOS operating systems; ClickShare CX-30 can turn small to medium-sized meeting rooms into innovative hybrid meeting spaces and conference facilities.

Find out what's new in the latest ClickShare update

Interact, discuss, collaborate with remote participants enjoying interactive hybrid meetings with touch back, annotation and blackboarding.

Bring your own meeting

ClickShare CX-30 brings seamless one-click wireless conferencing. With our agnostic wireless room system, you start a hybrid meeting from your laptop, using any conference tool for seamless Bring Your Own Meeting (BYOM) experiences.

Walk in, connect automatically to room devices like cameras, mics, speakers, sound bars. Make hybrid collaboration flow with only one click.

Start IT-friendly hybrid meetings

Decide how you and your guests collaborate. Plug & play with the ClickShare Button and choose for smart, intent-based meeting flows powered by the ClickShare App to make your meetings intuitive and interactive.

Enjoy interactivity features like local view of the room display, annotation, blackboarding and touch back support. ClickShare CX-30 is a fully integrated,



agnostic wireless conferencing room system that can be up and running in less than seven seconds. ClickShare can be used by anyone, including visitors and guests, and works with the largest range of solutions from our compatible brands and partners.

Better hybrid meetings? Yes! With smart, intuitive meeting flows in the ClickShare App

Smart intent-based meeting flows make your meeting experience stress-free. Walk into the room, you immediately see if the room is available or booked. Automatically connect to the meeting room (PresentSense ultrasound proximity detection) or plug in a Button. ClickShare guides you as a host or participant (HostFlow). Start the meeting from your personal calendar with a single click (One-Click-Join).

Share your presentation, keep track of remote participant's video, side by side (ConferenceView). Share full screen or application window, while keeping your laptop screen private for note taking. When you end the call, the meeting room becomes a digital signage display.

Matching your organization

A set of IT friendly features makes ClickShare Conference a perfect fit to any enterprise environment. ClickShare Conference, excelling in enhanced security, seamlessly integrates in any IT- network. With the XMS Cloud Management Platform you enjoy easy management of units, intuitive user experiences and clear analytics to drive your digital workplace.

For practical questions on network deployment of the ClickShare Conference range, check our technical support or get in touch with your Barco contact

You can have ClickShare in your meeting rooms without delay, thanks to strong inventory levels for all models.

PRODUCT SPECIFICATIONS**CLICKSHARE CX-30**

ClickShare Base Unit dimensions	
Dimensions (HxWxD)	34 mm x 135 mm x 135 mm
Power supply	Standard 110/220 V AC plug or USB-C
Power consumption	Operational: 5-10W, 24W Max
Weight	900 gr
General specifications	
Operating system	Windows 10 and higher macOS 11 (BigSur) and higher. Android v11 and higher (ClickShare App) iOS 14 and higher (ClickShare App)
System requirements	For a smooth experience with Microsoft Teams or Zoom. Minimum: Intel i3 dual-core processor / 8GB RAM / OS: Windows 10 latest build or Mojave latest build Recommended: Intel i5 4-core processor / 8GB RAM / OS: Windows 10 latest build or Mac OS latest build
Video outputs	4K UHD (3840*2160) @ 30Hz. HDMI 1.4b or USB-C DisplayPort 1.2
Audio output	USB, HDMI
USB	1 X USB-A, 1 X USB-C
ClickShare Buttons	2
ClickShare App	Desktop & Mobile
Native protocols	Airplay, Google Cast, Miracast
Maximum number of simultaneous connections (with Buttons and/or App)	32
Noise Level	Max. 25dBA @ 0-30°C Max. 30dBA @ 30-40°C
Authentication protocol	WPA2-PSK in stand alone mode WPA2-PSK or IEEE 802.1X using the ClickShare Button in network integration mode
Wireless transmission protocol	IEEE 802.11 a/g/n/ac and IEEE 802.15.1
Reach	Max. 30m (100 ft) between ClickShare Button and ClickShare Base Unit Frequency band 2.4 GHz and 5 GHz (DFS)
Frequency band	2.4 GHz and 5 GHz (DFS channels supported in select number of countries)
Connections	1x Ethernet LAN 1Gbit 1x USB Type-C 3.0 (front); 1x USB Type A 3.0 (front)
Temperature range	Operating: 0°C to +40°C (+32°F to +104°F) Max: 35°C (95°F) at 3000m Storage: -20°C to +60°C (-4°F to +140°F)
Humidity	Storage: 0 to 90% relative humidity, non-condensing Operation: 0 to 85% relative humidity, non-condensing
Anti-theft system	Kensington lock
Certifications	FCC/CE
Touch screen support & Interactivity	Yes
Wireless conferencing	via App or Button
Local view	Yes
Network connection	LAN & WiFi *
Management and reporting	Yes
Warranty	1 year standard. 5 years coverage via SmartCare

Last updated: 25 Jan 2023Technical specifications are subject to change without prior notice. Please check www.barco.com for the latest information.