

# ClickShare CX-30

Seamless wireless conferencing for small to medium-sized meeting and conference rooms



- Full BYOD support
- Remote collaboration with Button or Desktop App
- Works with your device, conferencing platform & a wide range of AV peripherals
- Enhanced security, connected and cloud managed
- Full interactivity

For meetings to be as productive as they can possibly be, participants need to feel engaged and inspired. ClickShare CX-30 from Barco offers a seamless wireless conferencing solution that can be used on any device to bring teams together—wherever they are in the world—to participate in inclusive meetings that generate the best ideas and discussion points. Compatible with any PC, laptop or Mac device running Windows, Android or iOS operating systems; ClickShare CX-30 can turn small to medium-sized meeting rooms into innovative meeting and conference facilities.

Find out what's new in the latest ClickShare update

Interact, discuss, collaborate with remote participants enjoying interactive meetings with touch back, annotation and blackboarding.

## Bring your own meeting

With ClickShare CX-30 you can start a meeting wherever you are with co-workers and stakeholders around the world. Complete with full Bring Your Own Device (BYOD) support, ClickShare CX-30 enables meeting participants to use whichever device they prefer, which makes remote collaboration a breeze when joining the meeting from another location, and when participating in the meeting from smaller meeting and huddle rooms where colleagues can use their laptops, tablets or even smartphones.

## Start IT-friendly remote meetings

ClickShare CX-30 is a fully integrated, wireless conferencing system that can be



up and running in less than seven seconds. The Conferencing Button and the ClickShare App help to make the whole process of sharing content quick and easy – ideal for when time is at a premium—while the agnostic nature of ClickShare helps to ensure it can be used by anyone, on any device with a wide range of USB peripherals.

ClickShare CX-30 is fully compatible with Windows, Mac, iOS and Android devices; and it can also be used alongside any unified communications (UC) technology and a wide range of AV USB peripherals. Also, ClickShare CX-30 users can benefit from interactive features\* including local view of the room display, annotation, blackboarding and touch back support allows users to control the touchscreen in the room.

With ClickShare CX-30 users can connect from whichever device they like, as the ClickShare CX-30 wireless conference system offers IT-friendly features including enhanced enterprise-grade security and seamless integration to protect data and the wider company network, as well as an XMS Cloud Management platform for easy device management and even analytics to ensure that you get the most out of your system and your meetings. For practical questions on network deployment of the ClickShare Conference range, check our technical support or get in touch with your Barco contact

**PRODUCT SPECIFICATIONS****CLICKSHARE CX-30**

ClickShare Base Unit dimensions	
Dimensions (HxWxD)	34 mm x 135 mm x 135 mm
Power supply	Standard 110/220 V AC plug
Power consumption	Operational: 5-10W, 24W Max
Weight	900 gr
General specifications	
Operating system	Windows 8/8.1/10. macOS 10.15 and higher. Android v11 and higher (ClickShare App) iOS 14 and higher (ClickShare App)
System requirements	For a smooth experience with Microsoft Teams or Zoom.  Minimum: <ul style="list-style-type: none"><li>■ Intel i3 dual-core processor</li><li>■ 8GB RAM</li><li>■ OS:<ul style="list-style-type: none"><li>● Windows 10 latest build</li><li>● Mojave latest build</li></ul></li></ul> Recommended: <ul style="list-style-type: none"><li>■ Intel i5 4-core processor</li><li>■ 8GB RAM</li><li>■ OS:<ul style="list-style-type: none"><li>● Windows 10 latest build</li><li>● Mac OS latest build</li></ul></li></ul>
Video outputs	4K UHD (3840*2160) @ 30Hz. HDMI 1.4b
Audio output	USB, HDMI
USB	1 X USB-A, 1 X USB-C
ClickShare Buttons	2
ClickShare App	Desktop & Mobile
Native protocols	Airplay, Google Cast, Miracast
Maximum number of simultaneous connections (with Buttons and/or App)	minimum 32
Noise Level	Max. 25dBA @ 0-30°C Max. 30dBA @ 30-40°C

**PRODUCT SPECIFICATIONS****CLICKSHARE CX-30**

<b>Authentication protocol</b>	WPA2-PSK in stand alone mode WPA2-PSK or IEEE 802.1X using the ClickShare Button in network integration mode
<b>Wireless transmission protocol</b>	IEEE 802.11 a/g/n/ac and IEEE 802.15.1
<b>Reach</b>	Max. 30m (100 ft) between ClickShare Button and ClickShare Base Unit Frequency band 2.4 GHz and 5 GHz (DFS)
<b>Frequency band</b>	2.4 GHz and 5 GHz (DFS channels supported in select number of countries)
<b>Connections</b>	1x Ethernet LAN 1Gbit 1x USB Type-C 2.0 (front); 1x USB Type A 2.0 (front)
<b>Temperature range</b>	Operating: 0°C to +40°C (+32°F to +104°F) Max: 35°C (95°F) at 3000m Storage: -20°C to +60°C (-4°F to +140°F)
<b>Humidity</b>	Storage: 0 to 90% relative humidity, non-condensing Operation: 0 to 85% relative humidity, non-condensing
<b>Anti-theft system</b>	Kensington lock
<b>Certifications</b>	FCC/CE
<b>Touch screen support &amp; Interactivity</b>	Yes
<b>Wireless conferencing</b>	via App or Button
<b>Local view</b>	Yes
<b>Network connection</b>	LAN & WiFi *
<b>Management and reporting</b>	Yes
<b>Warranty</b>	1 year standard. 5 years coverage via SmartCare

Last updated: 18 Oct 2021

Technical specifications are subject to change without prior notice. Please check [www.barco.com](http://www.barco.com) for the latest information.