

# ClickShare CX-20

Easy wireless conferencing for small meeting rooms and huddle spaces



- Full BYOD support
- Remote collaboration with Button or Desktop App
- Works with your device, conferencing platform & a wide range of solutions
- Enhanced security, connected and cloud managed

Organizations today requires smooth hybrid collaboration and flexibility, especially when it comes to team meetings in huddle rooms, and this is exactly what Barco ClickShare CX-20 provides. Encouraging creative innovation through seamless wireless conferencing, ClickShare CX-20 makes hybrid collaboration flow with one click..

Find out what's new in the latest ClickShare update

## Start a huddle meeting from your device

ClickShare CX-20 brings seamless one-click wireless conferencing. It's easier than ever to start hybrid huddle meetings from your device. With our agnostic wireless room system, you start a hybrid huddle meeting from your laptop, using your preferred conference tool, in less than seven seconds. Walk in, connect automatically to room devices like cameras, mics, speakers, sound bars, saving time and maximizing efficiency. Make hybrid collaboration flow with only one click. For employees and guests.

## Decide how you want to collaborate

ClickShare CX-20 provides you with exceptional flexibility and choice, enabling you to decide just how you want to collaborate. Plug & play with the ClickShare Button and choose for smart, intent-based meeting flows powered by the App to make your meetings intuitive and interactive. Both facilitate a user experience that's both straightforward and consistent. Enjoy useful features like local view of the room display and calendar integration.

ClickShare CX-20 is also tech-agnostic and fully compatible with your conferencing platform (UC) technology and a wide range of USB-peripherals. Additional features such as local view of the room display help you to optimize your one-click meeting experience.



### **Better hybrid meetings? Yes! With smart, intuitive meeting flows in the ClickShare App**

Smart intent-based meeting flows make your meeting experience stress-free. Walk into the room, you immediately see if the room is available or booked. Automatically connect to the meeting room (PresentSense ultrasound proximity detection) or plug in a Button. ClickShare guides you as a host or participant (HostFlow). Start the meeting from your personal calendar with a single click (One-Click-Join).

Share your presentation, keep track of remote participant's video, side by side (ConferenceView). Share full screen or application window, while keeping your laptop screen private for note taking. When you end the call, the meeting room becomes a digital signage display.

### **Enhanced security and seamless integration**

A set of IT friendly features makes ClickShare Conference a perfect fit to any enterprise environment. ClickShare Conference, excelling in enhanced security, seamlessly integrates in any IT- network. With the XMS (Cloud) Management Platform you enjoy easy management of units, intuitive user experiences and clear analytics to drive your digital workplace.

For practical questions on network deployment of the ClickShare Conference range, check our technical support or get in touch with your Barco contact.

**PRODUCT SPECIFICATIONS****CLICKSHARE CX-20**

<b>ClickShare Base Unit dimensions</b>	
Dimensions (HxWxD)	34 mm x 135 mm x 135 mm
Power supply	Standard 110/220 V AC plug
Power consumption	Operational: 5-10W, 24W Max
Weight	900 gr
<b>General specifications</b>	
Operating system	Windows 8/8.1/10/11 macOS 10.15 and higher. Android v11 and higher (ClickShare App) iOS 14 and higher (ClickShare App)
System requirements	For a smooth experience with Microsoft Teams or Zoom.  Minimum: Intel i3 dual-core processor / 8GB RAM / OS: Windows 10 latest build or Mojave latest build  Recommended: Intel i5 4-core processor / 8GB RAM / OS: Windows 10 latest build or Mac OS latest build
Video outputs	4K UHD (3840*2160) @ 30Hz, HDMI 1.4b
Audio output	USB, HDMI
USB	1 X USB-A, 1 X USB-C
ClickShare Buttons	1
ClickShare App	Desktop & Mobile
Native protocols	Airplay, Google Cast, Miracast
Maximum number of simultaneous connections (with Buttons and/or App)	32
Noise Level	Max. 25dBA @ 0-30°C Max. 30dBA @ 30-40°C
Authentication protocol	WPA2-PSK in stand alone mode WPA2-PSK or IEEE 802.1X using the ClickShare Button in network integration mode
Wireless transmission protocol	IEEE 802.11 a/g/n/ac and IEEE 802.15.1
Reach	Max. 30m (100 ft) between ClickShare Button and ClickShare Base Unit Frequency band 2.4 GHZ and 5 GHz (DFS)
Frequency band	2.4 GHZ and 5 GHz (DFS channels supported in select number of countries)
Connections	1x Ethernet LAN 1Gbit 1x USB Type-C 2.0 (front); 1x USB Type A 2.0 (front)
Temperature range	Operating: 0°C to +40°C (+32°F to +104°F) Max: 35°C (95°F) at 3000m Storage: -20°C to +60°C (-4°F to +140°F)
Humidity	Storage: 0 to 90% relative humidity, non-condensing Operation: 0 to 85% relative humidity, non-condensing
Anti-theft system	Kensington lock
Certifications	FCC/CE
Touch screen support & Interactivity	/
Wireless conferencing	via App or Button
Local view	Local view of the room display only
Network connection	LAN & WiFi *
Management and reporting	Yes
Warranty	1 year standard. 5 years coverage via SmartCare

Last updated: 16 Jun 2022

Technical specifications are subject to change without prior notice. Please check [www.barco.com](http://www.barco.com) for the latest information.