



# V9m

9mm pixel pitch, 4,000 nits LED display



- **Lightweight and slim**
- **Available in transparent version**
- **Unique magnetic lock for quick installation**

With the lightweight V9m LED display, rental companies have the flexibility to build large dynamic video backdrops for both indoor and outdoor stages, whether straight or curved, as well as side screens on lightweight trusses. What's more, the V9m is also ideally suited for overhead and ceiling screens and is available as transparent LED display as well.

### **Quick and easy to install**

The V9m comes with a special magnetic V-lock™, for reduced setup times and safe installation by one single person. A lightweight and slim LED display, the V9m can be boxed and shipped easily. Just like its V14m brother, the V9m shares its mechanics with the C series, so that rental companies that already own the Barco C series mechanics can reuse them.

### **Suited for outdoor stages**

The V9m can both be used indoors and outdoors, as it is equipped with the latest outdoor SMD technology. Moreover, it's rated IP65 which guarantees that it's fully waterproof.

### **High-performance scaling and control**

Just like the other V LED displays, the V9m is driven by the DV-100 image processor, which offers high-performance scaling and supports all the latest video standards (HDMI, DisplayPort, 3G SDI). In combination with the V series Toolset (VTS), the DV-100 allows for creative setups and remote control.

**PRODUCT SPECIFICATIONS****V9M**

|                         |  |
|-------------------------|--|
| Transparency            | 5% (transparent shader)<br>0% (non-transparent shader)   |
| Brightness              | 4,000 nits   |
| LED type                | 3-in-1 SMD   |
| Pixel density           | 11,025/sqm<br>1,024/sqft<br>7,056/tile   |
| Viewing angle           | H: 120 degrees<br>V: -60/+60 degrees (transparent shader)<br>V: -45/+60 degrees (non-transparent shader) |
| Contrast ratio          | 4,000:1 (transparent shader)<br>5,000:1 (non-transparent shader)   |
| Pixel pitch             | 9.52 mm  |
| Lifetime                | 50,000 hrs (@50 % brightness)  |
| Power consumption       | 516 W/sqm max.<br>206 W/sqm typical  |
| Operation power voltage | 200 -240V / 50 -60 Hz  |
| Tile size (WxHxD) in mm | 800 x 800 x 109 (31.5 x 31.5 x 4.3 inch)   |
| Weight                  | 13.5 kg/tile<br>29.8 lbs   |
| IP rating               | IP65   |
| Processing              | 16 bit/color   |
| Refresh rate            | Over 2,800 Hz  |
| Serviceability          | back   |
| Operatable digitizer    | DV-100   |
| Certifications          | CE, ETL, FCC Class A, TÜV, RoHS, WEEE  |

Last updated: 21 Jan 2018

Technical specifications are subject to change without prior notice. Please check [www.barco.com](http://www.barco.com) for the latest information.