

F80-4K12

12,000 lumens, 4K UHD, DLP laser phosphor projector



- **Stunning images with Rec. 709 color gamut**
- **Ultimate installation flexibility**
- **3D capable**

The stunning image quality and laser phosphor light source of Barco's F80 projectors enable you to provide exceptional experiences while saving both time and money. They're designed for fixed installation in a wide range of applications such as museums, board rooms, and auditoriums. Thanks to their 3D capability, they're also perfectly fit for theme park dark rides and interactive experiences.

Superior image quality

The F80-4K12 delivers stunning images at 4K UHD resolution with a high level of detail, and highly saturated colors that meet the Rec. 709 color space. What's more it features the powerful Barco Pulse processing that allows for sharper images and less latency thanks to its Single Step Processing (SSP).

Unprecedented business value

With this projector you can increase your uptime while driving costs down. Through its laser-phosphor light source and advanced cooling design, it provides a long operating time without need for lamp changes - resulting in considerable cost-savings on maintenance and consumables.

Ultimate installation flexibility

The F80-4K12 gives you more flexibility in projector location and orientation as it can run in any orientation. Thanks to its wide array of all-glass lenses and wide lens shift ranges, the F80-4K12 accommodates almost any projector configuration.

PRODUCT SPECIFICATIONS**F80-4K12**

Projector type	Single-chip DLP laser phosphor projector
Technology	0.67" DMD™ x1
Resolution	3,840 x 2,400 (4K UHD) / 2,716 x 1,600 (WQXGA+ native)
Brightness	11,300 center lumens 10,700 ANSI lumens 12,000 ISO lumens
Contrast ratio	1,200:1 sequential, 10,000:1 dynamic*
Brightness uniformity	> 90%
Aspect ratio	17:10 native
Blend	horizontal and vertical edge blending
Lens type	GLD / FLD+ (lens adapter needed) / FLDX (lens adapter needed)
Lens range	GLD-range: 0.8 -1.0 ; 1.0 -1.35 ; 1.35 -2.0 ; 2.0 -3.0
Screen size	max 20m
Optical lens shift	Vertical up to 125%, depending on lens Horizontal up to 50%, depending on lens Motorized zoom and focus (with lens memory on GLD and FLDX lenses) Motorized lens shift (with position memory on all lenses)
Color correction	P7 RealColor™
Light source	Laser phosphor
Light source lifetime	> 20000 h in normal mode, > 12000 h in silent mode, > 40000 h in long life mode, > 12000 h in high brightness mode
Sealed DLP™ core	Yes
Optical dowsler	Laser dimming
Orientation	360° rotation, no restrictions
DMX 512	Standard
Image processing	Embedded warp & blend engine direct adjust OSD + Ptoolset
CLO (constant light output)	Yes
3D	Active stereoscopic 3D / Passive stereo compatible max WQXGA @120Hz
Keystone correction	Yes
Inputs	HDMI2.0 (HDCP2.2, HDR10) / 2x DP 1.2 / 12G in (and 12G loop through) / 2x dual link DVI-D / HDBaseT
Input resolutions	From VGA up to 4K (4096 x 2160) refresh rates: 24Hz to 120Hz for WQXGA+ (2716x1600) and 24Hz to 60Hz for 4K/4KUHD (4096 x 2160/ 3860 x 2400)
Software tools	Projector Toolset
Control	TCP-IP / IR / RS-232 / XLR wired
Network connection	10/100 Base-T, RJ-45 connector
Power requirements	100-240V / 50-60Hz
Power consumption	1050 W nominal, 1200 W maximum
Standby power	< 0.5W
Noise level (typical at 25°C/77°F)	35 dB(A) when used in silent mode / 39 dB(A) in normal mode

PRODUCT SPECIFICATIONS**F80-4K12**

24/7 operation	Yes**
Operational ambient temperature	0°-35°C / 32°-95°F
Storage temperature	-20 to 60 °C
Operating humidity	0% -80% RH (non-condensed)
Storage humidity	20 -90% RH (non-condensed)
Dissipation BTU	max 4100 BTU/h
Dimensions (WxLxH)	480 x 680 x 227 mm / 18.9 x 26.7 x 8.9 in (without feet)
Weight	26.8 kg / 59.1 lbs (without lens)
Shipping Dimensions	583 x 754 x 444 mm / 23.0" x 30.9" x 17.5"
Shipping weight	38.5 kg / 81.6 lbs
Standard accessories	Power cord, wireless/XLR wired rugged remote control
Certifications	Compliant with UL60950-1 and EN60950-1 complies with FCC rules & regulations, part 15 Class A and CE EN55022 Class A, RoHS
Warranty	3 years***
Notes	* SW upgradable. Please contact an authorized Barco representative for details. ** For optimal performances, switch off the projector regularly, preferably twice a day if possible, by using the stand-by button ***except on light source: 20.000 hrs in normal mode or 3 years

Last updated: 15 Nov 2021

Technical specifications are subject to change without prior notice. Please check www.barco.com for the latest information.