

# FLD+ Long Focus 0.8 - 1.21 : 1 (EN45)



## Throw ratio

- SX+ 0.81-1.22:1
- 1080 / WUXGA 0.75-1.13:1
- Panorama / WQXGA 0.80-1.21:1
- Native 4K 0.70-1.06:1
- F80: 1.06-1.60 : 1 (WQXGA/4K UHD)  
(F80 requires the FLD/FLD+ lens adapter)

**PRODUCT SPECIFICATIONS****FLD+ LONG FOCUS 0.8 - 1.21 : 1 (EN45)**

---

<b>Working F/#</b>	F 2.4-3.29 Motorized Iris F# 2.4-6.5
<b>Zoom ratio</b>	1.51 Motorized zoom and focus
<b>Focal length</b>	15.85-23.93 mm
<b>Focus Range</b>	Optical performance 5-30 m
<b>Custom focus range</b>	Extended focus range is available, please contact sales for details
<b>Weight</b>	3.04 kg
<b>Throw Ratio</b>	DMD chip <ul style="list-style-type: none"><li>■ WQXGA 0.8-1.21:1</li><li>■ 1080p /WUXGA 0.75-1.13 :1</li><li>■ SXGA+ 0.81-1.22:1</li></ul>
	Image size tolerance +/-2%

---

**Last updated: 15 Nov 2022**

Technical specifications are subject to change without prior notice. Please check [www.barco.com](http://www.barco.com) for the latest information.