

FLD+ Long Focus 0.8 - 1.21 : 1 (EN45)

F35/F70/F90: 0.75 - 1.13 : 1 (WUXGA) / 0.8 - 1.21 : 1
(WQXGA/4K UHD)/ F80: 1.12 - 1.70 : 1 (WQXGA/4K UHD)



Throw ratio

- SX+ 0.81-1.22:1
- 1080 / WUXGA 0.75-1.13:1
- Panorama / WQXGA 0.80-1.21:1
- F80: 1.12 - 1.70 : 1 (WQXGA/4K UHD)
(F80 requires the FLD/FLD+ lens adapter)

PRODUCT SPECIFICATIONS**FLD+ LONG FOCUS 0.8 - 1.21 : 1 (EN45)**

Working F/#	F 2.4-3.29 Motorized Iris F# 2.4-6.5
Zoom ratio	1.51 Motorized zoom and focus
Focal length	15.85-23.93 mm
Focus Range	Optical performance 5-30 m
Custom focus range	Extended focus range is available, please contact sales for details
Weight	3.04 kg
Throw Ratio	DMD chip <ul style="list-style-type: none">■ WQXGA 0.8-1.21:1■ 1080p /WUXGA 0.75-1.13 :1■ SXGA+ 0.81-1.22:1
	Image size tolerance +/-2%

Last updated: 04 Jul 2019

Technical specifications are subject to change without prior notice. Please check www.barco.com for the latest information.