

FLD 1.6 - 2.32 : 1 (EN11)

1.74 - 2.51 : 1 (SX+) / 1.6 - 2.32 : 1 (WUXGA)



Focus range: 2.0 - 15.0 m

Throw ratio:

- SX+ 1.74-2.51:1
- 1080 / WUXGA 1.60-2.32:1

PRODUCT SPECIFICATIONS**FLD 1.6 - 2.32 : 1 (EN11)**

Working F/#	F 2.1-2.52 Motorized Iris F# 2.1-6.5
Zoom ratio	1.45 Motorized zoom and focus
Focal length	33.2-48.1 mm
Focus Range	Standard: 2m – 15m
Custom focus range	Extended focus range is available, please contact sales for details
Weight	2.2 kg
Throw Ratio	DMD chip <ul style="list-style-type: none">■ 1080p/WUXGA 1.6-2.32:1■ SXGA+ 1.74-2.51:1■ 720p 1.9-2.75:1■ XGA 2.37-3.43:1
	Image size tolerance +/-5%

Last updated: 13 Nov 2018

Technical specifications are subject to change without prior notice. Please check www.barco.com for the latest information.