

Long tele zoom EN26



Focus range: 5.0 - 25.0 m

- SX+ 4.30-6.89:1
- 1080 / WUXGA 3.90-6.24:1

PRODUCT SPECIFICATIONS**LONG TELE ZOOM EN26**

Working F/#	F 2.6-3.4 Voice coil operated Iris F 2.6-7.0
Zoom ratio	1.6 Motorized zoom and focus
Focal length	82.55-132.0 mm
Focus Range	Standard: 5-25 m
Custom focus range	Extended focus range is available, please contact sales for details
Weight	3.6 kg
Throw Ratio	DMD chip <ul style="list-style-type: none">■ SXGA+ 4.3-6.89 :1■ 1080p/Wuxga 3.9-6.24 :1

Image size tolerance +/-5%

Last updated: 16 Dec 2021

Technical specifications are subject to change without prior notice. Please check www.barco.com for the latest information.