

FLD+ 0.8 : 1 (EN42)

F35/F70/F90: 0.75 : 1 (WUXGA) / 0.8 : 1 (WQXGA/4K UHD)/
F80: 1.12 : 1 (WQXGA/4K UHD) (F80 requires the FLD/FLD+



Throw ratio

- SX+ 0.81:1
- 1080 / WUXGA 0.75:1
- Panorama / WQXGA 0.80:1
- F80: 1.12 : 1 (WQXGA/4K UHD)
(F80 requires the FLD/FLD+ lens adapter)

PRODUCT SPECIFICATIONS**FLD+ 0.8 : 1 (EN42)**

Working F/#	F 2.1 Motorized Iris F# 2.1-6.5
Focal length	16.12 mm
Focus Range	Optical Performance : 0.7m –7m Mechanical (0.5-10m)
Custom focus range	Extended focus range is available, please contact sales for details
Weight	2.7 kg
Throw Ratio	DMD chip <ul style="list-style-type: none">■ WQXGA 0.8:1■ 1080p /WUXGA 0.75:1■ SXGA+ 0.81:1■ Image size tolerance +/- 2%

Last updated: 13 Nov 2018

Technical specifications are subject to change without prior notice. Please check www.barco.com for the latest information.