

ClickShare C-5

Making presentation flow in small, medium meeting rooms and huddle spaces



- Full BYOD support
- Seamless content sharing with Button or Desktop App
- Enhanced security, connected and cloud managed

Your workplace requires seamless collaboration and the flexibility to easily share content, on screen, even in the smallest meeting rooms and huddle rooms in your company. ClickShare C-5 is the wireless presentation system that makes your meetings flow with one click in the ClickShare App, from any laptop or mobile device.

Find out what's new in the latest ClickShare update

Easily share content from your device

Start a huddle meeting within seconds. Anyone, including guests, can share content wirelessly to the central room display in full HD. With just one click in the ClickShare App, from any laptop (Windows or Mac) or mobile device for better workflow integration. Or with the ClickShare Button if you prefer a Plug&Play solution (sold separately). No cables, no training needed.

With full Bring Your Own Device (BYOD) support on a 4K canvas, our wireless presentation solution drives an easy collaborative experience in all your enterprise meeting rooms to make your content stick. We support screen mirroring with Airplay, GoogleCast and Miracast. Enjoy advanced collaboration features like view the room display on your own device or decide what you share, either your full screen or a single window.

Enhanced security and seamless integration

Designed for enterprise rollouts, the IT-grade C-5 offers you enhanced security features (ISO27001 certified) and a wide range of connectivity options. Use your display for digital signage content when not used for presenting thanks to signage integration options. With the XMS Cloud Management Platform you enjoy remote management of units and clear analytics to drive your digital workplace. For practical questions on network deployment of the ClickShare



range, check our technical support or get in touch with your Barco contact.

Boost collaboration in huddle or small meeting rooms

The ClickShare C-5 can be used as a stand-alone solution or in combination with your existing smaller meeting room setup. It empowers meetings with simple, one-click wireless content sharing in huddle spaces. ClickShare completes your room set-up and makes presentation easy, simple and wireless. Designed to fit your business perfectly and evolve with it. With flexibility for the future built in, it's one of the smartest investments you can make in your meeting room.

You can have ClickShare in your meeting rooms without delay, thanks to strong inventory levels for all models.

PRODUCT SPECIFICATIONS**CLICKSHARE C-5**

ClickShare Base Unit dimensions	
Dimensions (HxWxD)	34 mm x 135 mm x 135 mm
Power supply	Standard 110/220 V AC plug or USB-C (only Gen2)
Power consumption	Operational: 5-10W, 24W Max
Weight	900 gr
General	
Operating system	Windows 10 and higher macOS 11 (BigSur) and higher Android v9 and higher (ClickShare App)* iOS 12 and higher (ClickShare App)*
Video outputs	4K UHD (3840*2160) @ 30Hz. HDMI 1.4b or USB-C DisplayPort 1.2 (only Gen2)
Audio output	HDMI
USB	1 X USB-A, 1 X USB-C
ClickShare Buttons	0
ClickShare App	Desktop & Mobile
Native protocols	Airplay, Google Cast, Miracast
Maximum number of simultaneous connections (with Buttons and/or App)	32
Noise Level	Max. 25dBA @ 0-30°C Max. 30dBA @ 30-40°C
Authentication protocol	WPA2-PSK in stand alone mode WPA2-PSK or IEEE 802.1X using the ClickShare Button in network integration mode
Wireless transmission protocol	IEEE 802.11 a/g/n/ac and IEEE 802.15.1
Reach	Adjustable with signal strength modulation; max. 30m (100 ft) between ClickShare Button and ClickShare Base Unit Frequency band 2.4 GHZ and 5 GHZ
Frequency band	2.4 GHZ and 5 GHZ (DFS channels supported in select number of countries)
Connections	1x Ethernet LAN 1Gbi 1x USB-C 2.0 (front); 1x USB-A 2.0 (front) -only Gen2: 1x USB-C 3.0 (front); 1x USB-A 3.0 (front)
Temperature range	Operating: 0°C to +40°C (+32°F to +104°F) Max: 35°C (95°F) at 3000m Storage: -20°C to +60°C (-4°F to +140°F)
Humidity	Storage: 0 to 90% relative humidity, non-condensing Operation: 0 to 85% relative humidity, non-condensing
Anti-theft system	Kensington lock
Certifications	FCC/CE
Touch screen support & Interactivity	/
Room Dock (peripheral support)	No
Local view	Local view of the room display only
Network connection	LAN & WiFi
Management and reporting	Yes
Warranty	1 year standard. 5 years coverage via SmartCare
*	* depends on configuration, available in future firmware updates

Last updated: 27 Feb 2023

Technical specifications are subject to change without prior notice. Please check www.barco.com for the latest information.