


HDX-4K20 FLEX

19,000 lumens, 4K UHD, 3-chip DLP projector with flexible brightness and resolution



- **4K UHD resolution for smooth, sharp images with fine detail**
- **Choose the right brightness and resolution for your event**
- **Advanced warping and blending with zero additional latency**

The HDX-4K20 FLEX offers 4K UHD resolution for superb image quality. This projector shares its lens range, ease of use, and modularity with the other HDX models. Thanks to its modular design of only five building blocks the HDX-4K20 FLEX is easy to service. Equipped with rental frames, the projector can easily be stacked or rigged. The HDX-4K20 FLEX shares its TLD lens suite with the other RLM, HDX, HDF, and FLM projectors. What's more, the TLD+ 0.8-1.16:1 lens offers extreme 120% vertical lens shift capability.

Excellent image quality

Equipped with 3-chip DLP® technology, a single high-brightness Xenon lamp, and a high-contrast optical engine, the HDX-4K20 FLEX excels in brightness, color accuracy, and stability. Thanks to its 4K UHD resolution this projector delivers smooth, sharp images with fine detail.

Flexible brightness and resolution

The HDX-4K20 FLEX comes with Barco's unique flexible brightness feature, which allows you to tune and lock the brightness level for a specific application – from 10,000 to 19,000 lumens in incremental steps. It also includes flexible resolution, allowing you to choose and lock in WUXGA, WQXGA or 4K UHD resolution.

Scaling and input flexibility

Featuring a single-step processing electronics unit, the projector provides powerful scaling, handles all of the latest resolutions and offers advanced image warping and edge blending with zero additional latency. The HDX-4K20 FLEX supports HDMI 2.0, DisplayPort 1.2, HDBaseT and quad 6G HDSI inputs.

PRODUCT SPECIFICATIONS**HDX-4K20 FLEX**

| | |
|--|---|
| Projector type | 4K UHD 3-Chip DLP digital projector |
| Technology | 0.90" DMD x 3 with sealed DMD core |
| Resolution | 3,840 x 2,400 (4K UHD) / 2,560 x 1,600 (WQXGA native) / 16:10 aspect ratio |
| Light output | 19,000 (WQXGA) / 17,500 (4K UHD mode) center lumens |
| Contrast ratio | 1,900:1 (standard) -2,200:1 (high contrast mode) |
| Brightness uniformity | 90% |
| ScenergiX | horizontal and vertical edge blending |
| Lens range | TLD+ 0.37, 0.65-0.85, 0.8-1.16; 1.16-1.5:1; 1.5-2.0:1; 2.0-2.8:1; 2.8-4.5:1; 4.5-7.5:1; 7.5-11.5:1 |
| Optical lens shift | Vertical: -30% to +120%/Horizontal: -40% to +40% on zoom lenses (memorized) |
| Color correction | P7 |
| Lamps | 2.5 kW Xenon / lamp lifetime: 1,000 hours typical |
| Transport with lamp | Yes |
| Lamp house, quick replace | Yes |
| Customer bulb replace | Yes |
| Lamp warranty (field replace/ factory replace) | 90 days, 500 hours/pro rata 750 hours |
| Optical dowser | Standard |
| Picture-in-picture | Two sources simultaneously* |
| Orientation | table -ceiling -side (portrait) (lamp door down/bottom) -vertical |
| DMX 512 | Standard |
| WARP | direct adjust OSD + toolset |
| Image processing | Embedded warp & blend engine |
| Keystone correction | Yes |
| Integrated web server | Yes |
| CLO (constant light output) | standard |
| 3D | active eyewear (optional), passive Infitec (optional), passive circular (optional), 2 flash up to 200Hz* |
| Inputs | Single HDBaseT, HDMI2.0 (HDCP2.2, HDR10), DP 1.2, Quad 3G/12G SDI / BarcoLink |
| Optional Inputs | Quad DP1.2 |
| Input resolutions | From VGA up to 4K (4,096 x 2,160) |
| Pixel clock | 600Mhz |
| Software tools | Projection Toolset + Android app* + iOS app* |
| Control | 10/100 Base-T, RJ-45 conn, Wifi (opt), GSM (opt), XLR wired + IR , RS232, DMX 512* |
| AC power | 110-130V/200-240V, 50-60 Hz |
| Power consumption | 3,000 W / STBY |
| Noise level (typical at 25°C/77°F) | 53 dB (A) |
| Operating temperature | 0 ~ 40°C / 32 ~ 104°F |
| operation humidity no condens | 0% -80% |
| Dissipation BTU | Max. 5800 BTU/h @ (110-130V) / Max 9725 BTU/h |
| Dimensions (WxLxH) | 475 x 725 x 382 mm (18.70" x 28.54" x 14.96") |
| Weight | 50kg (110lbs) |
| Shipping Dimensions | (WxLxH) 650 x 900 x 560 mm (25.59" x 35.43" x 22.04") |
| Standard accessories | Power cord; wireless/XLR wired rugged remote control |
| Certifications | Compliant with UL60950-1 and EN60950-1, complies with FCC rules & regulations, part 15 Class A and CE EN55022 Class A, RoHS |
| Warranty | 3 years standard |
| * | SW upgradable. Please contact an authorized Barco representative for details. |

Last updated: 18 Jun 2019

Technical specifications are subject to change without prior notice. Please check www.barco.com for the latest information.