

DP2K-10S

Small DLP Barco Alchemy Cinema projector for screens up to 10m (33ft) wide



- **Integrated, DCI-compliant, future-proof projector**
- **Pristine image quality at a low TCO**
- **Combines media server functionalities with Series 3 cinema processing electronics**

The DP2K-10S projector is a compact, fully integrated digital cinema projector designed for smaller theaters, boothless cinemas and single screens. By merging the projector and media server functionalities into one single projector module, the DP2K-10S Barco Alchemy projector is a full-fledged, DCI-compliant projector and media-server solution that includes on-board storage. Reducing the required hardware, it increases simplicity and reliability in the projection booth. And for additional reliability, the smart projector detects potential operational errors and warns users if, for instance, a scheduled show is missing assets or KDMs. Great in TMS environments, it operates stand-alone in single-screen applications. Thanks to the embedded Barco Web Commander user interface, shows can be created and scheduled remotely.

Ultimate image quality

Built upon Barco's renowned DP2K cinema projectors, the DP2K-10S guarantees crisp images over time thanks to its acclaimed manual color convergence mechanism. While its standard Xenon lamps offer vibrant colors, its motorized lenses ensure a perfect image ratio at all times.

Low cost of ownership

Geared with integrated technology that drives operational and maintenance costs down, the DP2K-10S offers pristine images and ultimate reliability at a low TCO. As such, it is the perfect choice for exhibitors looking for a worry-free solution to go digital with a minimal hassle and risk.

The DP2K-10S projector is also available in a package with a third-party media server and it can be ordered without the Barco Alchemy module as well.

Unique benefits of Barco Alchemy technology



PRODUCT SPECIFICATIONS**DP2K-10S**

Preliminary technical specifications. These are subject to change without prior notice.

Digital MicroMirror Device™	3 x 0.69" DC2K dark metal devices
Native resolution	2,048 x 1,080 pixels
Housing	Hermetically sealed DMDs and optical assembly
Lamp	2.2kW, short-arc Xenon
Light output	9,000 lumens
Screen size	Up to 10m/33 ft wide (screen gain 1.2 @ 14ft)
Contrast ratio	1,850:1
Prime lenses	Fully motorized 1.2 - 1.7 1.34 - 1.9 1.5 - 2.15 1.7 - 2.55 2.0 - 3.9
Control I/O	3x Ethernet (RJ 45) 8x GPIO (DB 25) 3D interface USB interface
Integrated Cinema Media Processor	DCI 4K 2D up to 60fps* DCI 4K 3D (24 or 30 fps per eye)* DCI High Frame Rates 2K 3D up to 120fps (60fps per eye) JPEG 2000 bit-rates up to 625Mbps Dual-channel color-correction MPEG-2 (4:2:0 and 4:2:2 up to 60fps) 2x HDMI2.0a (up to 4K 2D 60fps) 2x 3G-SDI inputs 16x AES/EBU audio channels (2x RJ45) 8x GPI, 8x GPO (4x RJ45) 2x Gbe for content connectivity & ingest 2x front-accessible USB 3.0 for fast ingest 2x front-accessible USB 2.0 Video watermarking: Civolution NexGuard Audio watermarking: Civolution Closed captioning devices: Support for SMPTE 430-10 * 4K 24fps is standard. For 4K 60 fps / 4K 3D on ICMP upgrade modules a license is required. Newly-built 4K Barco Alchemy projectors have the license standard included.
Integrated storage	1.9TB effective storage (RAID-5) / 3x 1TB Hot-swappable 2.5" hard-drives 3.9TB effective storage (RAID-5) / 3x 2TB Hot-swappable 2.5" hard-drives
Barco Web Commander	Projector Dashboard Projector Control Board Show Player/Editor/Scheduler Automation, 3D, Ingest Dynamic DCP playlists & intermission TMS integration Smart Projector Status Via HTML5 web-browsers including iOS & Android tablets Dual projector 3D: passive and active Auro 11.1 decoding
Barco Communicator	Projector installation & configuration Projector update & maintenance
Power requirements	220 V
Projector dimensions (HxWxD)	325 x 626 x 925 mm 12.8 x 24.7 x 36.4 inch
Projector weight	Recessed handles for easy carrying 56.5 kg / 125 lbs for carrying (lamp-house removed) (66.5 kg / 147 lbs total weight)

PRODUCT SPECIFICATIONS**DP2K-10S**

Ambient temperature	35°C / 95°F Max.
Exhaust airflow	140 – 180 CFM (4 – 5 m ³ /min)
Options	Barco CineMate App (iOS & Android) - free 3D add-ons Touch screen monitor, inc. Barco Commander & Communicator Pedestal CineCare Web Auro 11.1 license Barco Escape license Dual-Projector license Live 3D*** *** Software roadmap

Last updated: 21 Jan 2018

Technical specifications are subject to change without prior notice. Please check www.barco.com for the latest information.