

# ClickShare CSM-1

Wireless presentation system - Barco ClickShare - CSM-1



ClickShare is Barco's wireless presentation and collaboration system, that allows any meeting participant to share content on the central meeting room screen.

### **An unmatched user experience**

At the click of a button, the content of your laptop, tablet or smartphone is displayed on the large screen. The result is that all participants are involved more intensely in the decision-making process. Coupling extreme simplicity with an unmatched user experience, everybody who has used ClickShare is immediately hooked. The system's stability and ease-of-use, also drastically limits the number of needed interventions by the IT department.

### **Instantly on screen, using any device**

A ClickShare CSM-1 set consists of two USB-powered devices, ClickShare Buttons, and a Base Unit. The Base Unit has a fixed connection to the meeting room's visualization system, and takes care of all the needed processing. Users who want to get their presentation on the large meeting room screen, simply connect a Button to their PC or MAC. They start the application, click the ClickShare Button and immediately their desktop is wirelessly transferred to the large visualization system. Alternatively, when using a smartphone or tablet (either iOS or Android-powered), a simple app allows you to share content as well. A maximum of two people can show their content on-screen simultaneously.

**PRODUCT SPECIFICATIONS****CLICKSHARE CSM-1**

<b>ClickShare Base Unit dimensions</b>	
<b>Weight</b>	530g / 1.17lbs (incl. antennas)
<b>Dimensions (HxWxD)</b>	Excl. antennas: 37mm x 186mm x 85mm / 1.457" x 7.323" x 3.346" Incl. antennas: 125mm x 186mm x 121mm x / 4.921" x 7.323" x 4.763"
<b>Power consumption</b>	Standby 3.5 W Operation typical: 6W Maximum: 7.5 – 9.7W
<b>General specifications</b>	
<b>AirPlay Support</b>	iOS mirroring (AirPlay) from iOS 9.0 up to iOS 10.2 / macOS 10.12 El Capitan
<b>Google Cast Support</b>	Google Cast not supported
<b>Operating system</b>	Windows 7/8/8.1/10 32 & 64 bit macOS 10.10/10.11/10.12 (Sierra) Android v5 & v6 (ClickShare app) iOS 8 & 9 (ClickShare app)
<b>Video outputs</b>	HDMI (video and audio), 15-pin VGA
<b>Frame rate</b>	Up to 30 fps depending on environment
<b>Output resolution</b>	HDMI: 1280x720 (720P), 1920x1080 (1080p) VGA: SVGA (800x600) / XGA (1024x768) / WXGA(1280x768) / WXGA+(1280x800) / 1360 * 768 / 1440 * 900
<b>Number of sources simultaneous on screen</b>	2 (2 via Buttons, 1 from mobile device)
<b>Number of simultaneous connections</b>	8
<b>Audio</b>	Radio quality 16bits 22KHz (no synchronization) via audio jack or HDMI
<b>iPad, iPhone and Android compatibility</b>	Available via ClickShare Presenter app for static content.
<b>Extended desktop</b>	Available (depending on the driver of your graphics card)
<b>Authentication protocol</b>	WPA2-PSK
<b>Wireless transmission protocol</b>	IEEE 802.11 a/b/g/n
<b>Data rate wireless</b>	Up to 300Mbps
<b>Reach</b>	Max. 30m (100 ft) between ClickShare Button and ClickShare Base Unit
<b>Frequency band</b>	2.4 GHz and 5 GHz (DFS channels not supported)
<b>Power</b>	External Power adaptor 5V DC input 2.6A (included in set)
<b>Connections</b>	USB Host x 2 RJ-45 LAN Port Audio analog line out on mini jack socket (3.5mm)
<b>Temperature range</b>	Operating: 0°C to +40°C (+32°F to +104°F) Storage: -10°C to +60°C (+14°F to +140°F)
<b>Humidity</b>	Storage: 0 to 90% relative humidity, non-condensing Operation: 0 to 80% relative humidity, non-condensing
<b>Wall mounts</b>	Included in set
<b>Certifications</b>	FCC/CE
<b>Warranty</b>	3 years standard Possible to extend to 5 years

Last updated: 13 Jun 2019

Technical specifications are subject to change without prior notice. Please check [www.barco.com](http://www.barco.com) for the latest information.