

iQ Pro G350

Barco's Network Centric LCD projector with XGA resolution and an amazing brightness level of 3,500 ANSI lumens.



ESPECIFICACIONES TÉCNICAS**IQ PRO G350**

Light output	3,500 ANSI lumens
Resolution	XGA (1024 x 768)
Brightness uniformity	> 95 % for the total screen
Contrast ratio	> 800:1 (full white/full black)
Display	3 active matrix 1.4" diagonal XGA polysilicon LCD panels with Micro Lens Arrays and a resolution of 1024 x 768 pixels (aspect ratio 4:3).
Features	<ul style="list-style-type: none">■ AutoImage■ Advanced picture-in-picture■ Seamless switching with effects■ Standard cable basket■ Standard light shutter■ Advanced digital zoom
Picture-in-picture	Up to 3 sources simultaneously
Inputs	<ul style="list-style-type: none">■ 1x Configurable 5-Wire (BNC) for: Composite Video, S-Video, Component Video , RGBHV, RGBS, RGsB.■ 1x Composite Video (BNC) (up to 7 Composite Video's when using all connectors on top input board)■ 1x S-Video (4-pin mini-DIN) (up to 3 S-Video's when combining BNC's)■ 1x VGA (D15 connector)■ 1x DVI (Digital Visual Interface)
Outputs	No output
Communication	1 x D9 connectors for RS232 In/Out 1 x spherical IR receiver
Compatibility	<ul style="list-style-type: none">■ All current video sources (PAL, SECAM, NTSC) in Composite, S-VHS, Component or RGB formats■ All currently proposed HDTV, extended and improved television standards (1080i, 720p)■ All computer graphics formats from VGA, SVGA, XGA, SXGA to UXGA■ Most Macintosh computers■ Electronic workstations with a resolution up to 1600 x 1200 pixels at 75 Hz■ Most computer sources with a pixel clock up to 160 MHz■ DVI sources up to SXGA+
Input source compatibility	1600 x 1200 (max. input)
Screen size	From 1-6m / 3-20ft.
Scan Frequencies	Horizontal 15kHz -110 kHz Vertical 25 Hz -150 Hz
Network connection	1 x 10/100 Base-T Ethernet
On board display server	Server Specifications: -Processor: Pentium M 1,6 GHz -Memory: 512 MB DDR RAM -Storage: 40 GB hard disk -Inputs and outputs: <ul style="list-style-type: none">■ PCMCIA slot for Wireless LAN cards, memory cards, Bluetooth, input extensions ...■ RJ45connector for Ethernet (10Mb/s) and Fast Ethernet (100Mb/s)4 USB connectorsAudio: 3,5 mm jacks for Microphone in, Line in and Line out
Ambient temperature	5°C up to 40°C
Lamp	2 x 250 Watt UHP lamp, in lamp housing, pre-aligned for max. light output. Typical lifetime: 3000 h/lamp. 3000 hours in Dual Lamp Mode or max. 6000 hours/set in Single Lamp Mode.
Lenses	Fixed focal length lenses are available with a throw ratio of 0.85:1 (very short throw ratio, specially designed for rear screen on-axis projection) or 7.0:1 (long throw). Variable focus lenses with a throw distance of 1.3-1.8, 1.9-2.6, 3.0-6.0 times the screen width.(2.5% tolerance)

ESPECIFICACIONES TÉCNICAS**IQ PRO G350**

Lens Shift	QVD lenses Motorized V shift: -30% +110% For specific details per lens type: see lens product pages
Lens encoders	Not Applicable
ScenergiX	Not Applicable
Sealed DLP™ core	Not Applicable
Dust filters	High Quality Microfilter (side removeable)
Noise Level	< 37dB
Mains Voltage	90V-255V
Power consumption	Max. 550 Watt
Power Dissipation	Max. 1878 BTU/h
AC power	Power factor pre-regulated SPMS, 90-254 VAC / 50-60Hz
Weight	Net weight: Body only 12.9kg / 28.5 lbs. Shipping weight: • without lens: max.17.5 kg / 28.5 lbs. • with lens: max. 20 kg / 44 lbs.
Dimensions	Projector body with cable basket: 415 mm (max. W) x 195 mm (max. H) x 565 (max. D) Projector body without cable basket: 415 mm(max. W) x 195 mm (max. H) x 487 (max. D)
Safety Regulations	Compliant with UL1950 and EN60950
Electromagnetic Interference	Compliant with FCC rules & regulations, part 15 Class B and CE EN55022 Class B

Generado en: 21 Jan 2018

Las especificaciones técnicas pueden estar sujetas a cambios sin previo aviso. Consulte www.barco.com para obtener la información más actual.