

SLM G5 Executive



TECHNICAL SPECIFICATIONS**SLM G5 EXECUTIVE**

Salida de luz	5,000 ANSI lumens
Digital MicroMirror Device™	three XGA DMDs (1024 x 768)
brillo uniforme	Brightness uniformity: >90% for the total screen
resolución	1.024 x 768 (nativo)
contraste	> 500:1 (full white/full black)
características	<ul style="list-style-type: none">■ Imagen en imagen■ Conmutación perfecta de fuentes con efectos
consumo de potencia	1600 Watt
compatibilidad	All video sources in Composite, S-VHS, Component or RGB formats or serial digital format All currently proposed HDTV, extended and improved television standards Most Macintosh computers Computers and electronic workstations with a resolution up to 1600 x 1200 pixels Two digital input slots allow direct digital interfacing with current and future digital inputs
dimensiones (ancho x largo x alto)	529 x 795 x 429 mm (20.8 x 31.3 x 16.9 inch)
lámpara	1.2 kW Xenon illumination system
desplazamiento de lente	TLD Lenses Motorized V shift: -20% +118% Motorized H shift: max. 65% (L+R) For specific details per lens type: see lens product pages
lentes	Fixed focal length lenses are available with a throw ratio of 0.8:1 (very short throw ratio, specially designed for rear screen on-axis projection) or 1.2:1 (long throw). Motorized Zoom Lenses with a throw distance of 1.6-2.0,2.0-2.8,2.8-5.0,5.0-8.0 times the screen width
conexión de red	Optional
ScenergiX	Optional
tamaño de pantalla	5 -15 m / 6 -50 ft
núcleo DLP? estanco	Optional
Conmutación fluida	Estándar
peso	Peso neto: 45 kg / 99 lbs

Generado en: 16 Jun 2022

Las especificaciones técnicas pueden estar sujetas a cambios sin previo aviso. Consulte www.barco.com para obtener la información más actual.