

PDS-4K Audio and DisplayPort 1.2 input card



- Adds Audio pass-through and Dante capability to the system
- Adds two more input connectors

Adds the ability for the PDS-4K to pass embedded audio from HDMI/DisplayPort/SDI input* to Program outputs and embed/disembed to Dante network audio.

Adds two DisplayPort 1.2 input connectors.

*SDI input and output supported in future software release

TECHNICAL SPECIFICATIONS**PDS-4K AUDIO AND DISPLAYPORT 1.2 INPUT CARD**

conectores	2x entradas DisplayPort 1.2 2x RJ-45 (Dante)
resolución	3840x2400p @60
Profundidad de color	10 bits
Muestreo de color	4:4:4
HDCP	1.x
Capacidad de señal	660 MHz
Canales de audio	2 por entrada o salida
Frecuencia de muestreo de audio	48 Khz
Profundidad de bits de audio	16 bits o 24 bits
Formato de audio	PCM
Compatible con AES 67	Sí
Número de canales Dante	64 entradas x 64 salidas (2 canales por entrada o salida)
características	Salidas seleccionables entre entrada específica, Dante Audio o Audio sigue al vídeo Retorno de audio PGM a Dante Todas las entradas transmiten a Dante

Generado en: 16 May 2022

Las especificaciones técnicas pueden estar sujetas a cambios sin previo aviso. Consulte www.barco.com para obtener la información más actual.