

Lente FLDX 0.38 : 1 UST 90°

WUXGA 1,12-1,58:1 WQXGA/4K 1,20-1,70:1 F80: 1,68-2,38: 1 (WQXGA/4K UHD) (F80 requiere el adaptador para lentes FLD/FLD+)



TECHNICAL SPECIFICATIONS**LENTE FLDX 0.38 : 1 UST 90°**

Platforms	F35, FL40, F70, F80*, F90 and G100** *For use with F80: Lens requires lens adapter (R98014421) **For use with G100: Lens needs lens adapter (R9802360) and lens support system (R9802365)
Working F/#	2.4
Zoom ratio	NA (fixed focal lens)
Focal length	8.2mm
Focus Range	Standard 133" – 400" for F80, 200" – 600" for F35, FL40, F70, F90 and G100
Weight	6.6kg
Shipping weight	9.7kg
Throw Ratio	DMD chip WUXGA (F35, FL40, F70, F90 and G100): 0.38 : 1 WQXGA (F35, FL40, F70 and F90): 0.41 : 1 WQXGA+ (F80): 0.54 : 1 Image size tolerances +/-2%

Generado en: 15 Mar 2021

Las especificaciones técnicas pueden estar sujetas a cambios sin previo aviso. Consulte www.barco.com para obtener la información más actual.