

iQ Pro R200L



TECHNICAL SPECIFICATIONS**IQ PRO R200L**

Salida de luz	1,800 ANSI lumen
brillo uniforme	>95 % for the total screen
relación de contraste	>400 : 1 (full white/full black)
Paneles LCD	3 active matrix 1.3" diagonal XGA polysilicon LCD panels with Micro Lens Arrays and a resolution of 1366 x 1024 pixels (aspect ratio 4:3).
resolución	1366 x 1024 (native)
Red	iQ Pro Server Specifications: -Processing Power: Pentium III socket with 1,2 Gigahertz Tualatin Celeron processor - Memory: 256 MB RAM -Storage: 40 GB hard disk -Video memory up to 64 MB -Inputs and outputs <ul style="list-style-type: none"> ■ PCMCIA slot for Wireless LAN cards, memory cards, Bluetooth, input extensions ... RJ45 connector for Ethernet (10Mb/s) and Fast Ethernet (100Mb/s) 4 USB connectors Audio: 3.5 mm jacks for Microphone in, Line in and Line out
características	· Advanced picture-in-picture · Seamless switching with effects · Standard cable basket · Standard light shutter · Advanced digital zoom
compatibilidad	The iQ Pro R200L is compatible with: <ul style="list-style-type: none"> ■ All current video sources (PAL, SECAM, NTSC) in Composite, S-VHS, Component or RGB formats All currently proposed HDTV, extended and improved television standards (1080i, 720p) All computer graphics formats from VGA, SVGA, XGA, SXGA to UXGA Most Macintosh computers Electronic workstations with a resolution up to 1600 x 1200 pixels at 75 Hz Most computer sources with a pixel clock up to 160 MHz DVI sources up to SXGA
tamaño de pantalla	From 1-6 m/3-20 ft.
entradas	1x Configurable 5-Wire (BNC) for: Composite Video, S-Video, Component Video, RGBHV, RGBS, RGB. 1x Composite Video (BNC) (up to 7 Composite Video's when using all connectors on top input board) 1x S-Video (4-pin mini-DIN) (up to 3 S-Video's when combining BNC's) 1x VGA (D15 connector) 1x DVI (Digital Visual Interface)
lámpara	2x 120 Watt UHP lamp, in lamp housing Typical lifetime: 6000 h/lamp. 6000 hours in Dual Lamp Mode or max. 12000 hours/set in Single Lamp Mode
lentes	Fixed focal length lenses are available with a throw ratio of 0.85:1 (very short throw ratio, specially designed for rear screen on-axis projection) or 7.0:1 (long throw). Variable focus lenses with a throw distance of 1.3-1.8, 1.9-2.6, 3.0-6.0 times the screen width
frecuencias de barrido	Horizontal 15 kHz -110 kHz Vertical 25 Hz -150 Hz
desplazamiento de lente	V shift: -30% +120%
dimensiones (ancho x largo x alto)	Projector body with cable basket: 415 mm (Max W) x 195 mm (Max H) x 565 mm Projector body without cable basket: 415 mm (Max W) x 195 mm (Max H) x 487 mm (Max D)
peso	Net weight, body only: 12.9kg/28.5 lbs.
comunicación	1x D9 connectors for RS232 In/Out 1x spherical IR receiver
nivel de ruido	
corriente alterna	Power factor pre-regulated SMPS, 90-254 VAC / 50-60Hz
consumo de potencia	Max 380 Watt
disipación de potencia	Max 1297 BTU/h
regulación de seguridad	Compliant with UL1950 and EN60950
interferencia electromagnética	BARCO's iQ Pro R200L complies with FCC rules & regulations, part 15 Class B and CE EN55022 Class B
Conmutación fluida	Standard

Generado en: 21 Jan 2018

Las especificaciones técnicas pueden estar sujetas a cambios sin previo aviso. Consulte www.barco.com para obtener la información más actual.