

# SLM R8 Performer

A Compact Projector for Rental & Staging Applications



**ESPECIFICACIONES TÉCNICAS****SLM R8 PERFORMER**

Light output	8.000 ANSI Lumen
Digital MicroMirror Device™	3 high resolution SXGA DMD™s
Resolution	1280 x 1024 (SXGA)
Brightness uniformity	> 90 % for the total screen area
Contrast	Normal mode: 800:1 High mode: 1600:1 (Full White/Full Black)
Lamp	Lifetime (max): 1000 Hrs Lifetime (typ): 500 Hrs  Lamp Power: 2,0 kW
Noise level (@ 20°C -68°F)	
Noise level (@ 40°C -104°F)	
Mains Voltage	200 -240 V
Power consumption	2.550 W
Ambient temperature	35°C (95F) max
Size	875 mm x 585 mm x 429 mm 34,5" x 23" x 16,9"
Weight (including rigging gear)	57 kg (126 lbs)
Lenses	BARCO's "click-and-play" TLD lenses provide the highest quality picture. Available both in fixed and zoom versions.
Lens Shift	Motorized V shift: up to 100% Motorized H shift: up to 65%
Sealed DLP™ core	No
Seamless Switching	Standard
ScenergiX	Standard
Network connection	Optional
Fixed Inputs	· 2 Multifunctional 5-cable inputs for the connection of RGB analogue signals with standard sync (BNC connectors) or tri-level sync, sync on green or separate sync, Standard Video signals, S-VHS signals  · 2 Multistandard DVI  · SDI input (Serial Digital Input)
Optional Inputs	One free digital input slot for optional input modules:  · SDI  · HD -SDI
Remote control	· RS232 or RS422 loop-through input (D9-connector) for PC based projector control  · Communication input (D9-connector) for peripherals  · 3 pin male XLR connector for wired remote (standard remote)  · 3 pin female XLR connector for bi-directional communication (rugged remote)

Generado en: 24 Feb 2021

Las especificaciones técnicas pueden estar sujetas a cambios sin previo aviso. Consulte [www.barco.com](http://www.barco.com) para obtener la información más actual.