

# SLM G8 Performer

A compact and Powerful Projector for Rental & Staging Applications



**TECHNICAL SPECIFICATIONS****SLM G8 PERFORMER**

Light output	8.000 ANSI Lumen
Resolution	1024 x 768 (native) 1600 x 1200 (max)
Resolution	1024 x 768 (native) 1600 x 1200 (max)
Digital MicroMirror Device™	3 high resolution XGA DMD's
Brightness uniformity	> 90 % for the total screen area
Contrast	Normal mode: 500:1 High mode: 1000:1 (Full White/Full Black)
Lamp	Lifetime (max): 1000 Hrs Lifetime (typ): 500 Hrs  Lamp power: 2,0 kW
Noise level (@ 20°C -68°F)	
Noise level (@ 40°C -104°F)	
Mains Voltage	200 -240 V
Power consumption	2.550 W
Ambient temperature	35°C (95F) max
Size	875 mm x 585 mm x 429 mm 34,5" x 23" x 16,9"
Weight (including rigging gear)	57 kg (126 lbs)
Lenses	BARCO's "click-and-play" TLD lenses provide the highest quality picture. Available both in fixed and zoom versions.
Lens Shift	Motorized V shift: up to 118% Motorized H shift: up to 65%
Sealed DLP™ core	No
Seamless Switching	Standard
ScenergiX	Standard
Network connection	Optional
Fixed Inputs	· 2 Multifunctional 5-cable inputs for the connection of RGB analogue signals with standard sync (BNC connectors) or tri-level sync, sync on green or separate sync, Standard Video signals, S-VHS signals  · 2 Multistandard DVI  · SDI input (Serial Digital Input)
Optional Inputs	One free digital input slot for optional input modules:  · SDI  · HD -SDI
Remote control	· RS232 or RS422 loop-through input (D9-connector) for PC based projector control  · Communication input (D9-connector) for peripherals  · 3 pin male XLR connector for wired remote (standard remote)  · 3 pin female XLR connector for bi-directional communication (rugged remote)

Generado en: 21 Jan 2018

Las especificaciones técnicas pueden estar sujetas a cambios sin previo aviso. Consulte [www.barco.com](http://www.barco.com) para obtener la información más actual.