

# NH-12

Proyector de 1080 píxeles HD, 12.000 lúmenes y tres chips DLO orientado a la red



**TECHNICAL SPECIFICATIONS****NH-12**

Light output	12,000 center lumens (+/-10%)
Contrast ratio	2,000:1
Resolution	Full 1080p HD
Chip type	Three-chip DLP
Lamp	2kW xenon
Lamp lifetime (typical)	750h warranted, max. 1000h
Weight	70kg (154.2lbs) net / 85kg (187.4lbs) shipping weight
Lens range	<ul style="list-style-type: none"><li>▪ Horizontal shift up to +/- 65%</li><li>▪ Vertical shift up to +/- 100%</li></ul>
Standard inputs	<ul style="list-style-type: none"><li>▪ 1x 5-BNC (RGBHV, RGBS or RGBsB)</li><li>▪ 1x composite video (BNC)</li><li>▪ 1x S-video (4-pin mini DIN)</li><li>▪ 1x DVI</li><li>▪ 1x VGA (D15)</li></ul>
Optional Inputs	<ul style="list-style-type: none"><li>▪ SD/HD-SDI output</li></ul>
Communication Port	<ul style="list-style-type: none"><li>▪ RS-232 (on D9)</li><li>▪ IR or wired remote</li><li>▪ 10/100 Mb/s Ethernet (on RJ45)</li></ul>
Video	<ul style="list-style-type: none"><li>▪ PAL, SECAM and NTSC signals</li><li>▪ Composite, S-video, component or RGB formats</li><li>▪ All current HDTV standards (720i, 720p, 1080i, 1080p)</li></ul>
Data	<ul style="list-style-type: none"><li>▪ All computer graphics formats up to QXGA at 75Hz</li><li>▪ Analog sources with a pixel clock of up to 270MHz</li><li>▪ DVI sources with a pixel clock of up to 165MHz</li></ul>
Safety	<ul style="list-style-type: none"><li>▪ ETL60950 and EN60950</li><li>▪ CE compliant</li><li>▪ CCC compliant</li></ul>
AC power	200 -240 VAC / 50-60Hz
Max. power consumption	2,800 Watt / 9,560 BTU
Special Features	<ul style="list-style-type: none"><li>▪ Keystone and linearity correction</li><li>▪ Optional full geometry correction</li><li>▪ Sealed, liquid-cooled engine</li><li>▪ Desktop output including external source windows on DVI-D</li></ul>

Generado en: 20 Dec 2018

Las especificaciones técnicas pueden estar sujetas a cambios sin previo aviso. Consulte [www.barco.com](http://www.barco.com) para obtener la información más actual.