

Télézoom court EN14

2,56 - 4,1 : 1 (SX+) / 2,37 - 3,79 : 1 (WUXGA)



Plage de mise au point : 3,0 - 30,0 m

- 2,57 - 4,10 : 1 (SXGA+)
- 2,37 - 3,79 : 1 (1080p)
- 2,37 - 3,79 : 1 (WUXGA)

SPÉCIFICATIONS TECHNIQUES**TÉLÉZOOM COURT EN14**

Working F/#	F 2.1-2.72 Motorized Iris F# 2.1-6.5
Zoom ratio	1.6 Motorized zoom and focus
Focal length	49.1-78.6 mm
Focus Range	Standard: 3.0m – 30m
Custom focus range	Extended focus range is available, please contact sales for details
Weight	2.5 kg
Throw Ratio	DMD chip <ul style="list-style-type: none">■ 1080p/WUXGA 2.37-3.79:1■ SXGA+ 2.56-4.1:1■ 720p 2.8-4.49:1■ XGA 3.5-5.6:1
	Image size tolerance +/-5%

Créé le : 21 Jan 2018

Les spécifications techniques sont susceptibles d'être modifiées sans préavis. Veuillez consulter les dernières informations disponibles sur www.barco.com.