

# FLDX 1,2 - 1,7 : 1 (EN63)

WUXGA 1,12-1,58:1 WQXGA/4K 1,20-1,70:1 F80 : 1,59 - 2,24 : 1 (WQXGA/4K UHD) (F80 nécessite l'adaptateur lentille FLD/FLD+)



**SPÉCIFICATIONS TECHNIQUES****FLDX 1,2 - 1,7 : 1 (EN63)**

<b>Platforms</b>	For F35, FL40, F70, F80* and F90 projector series *requires lens adapter R98014421. F80 specific throw ratio: 1.59 -2.24 : 1 (WQXGA/4K UHD)
<b>Working F/#</b>	F 2.4-2.7 Motorized Iris F# 2.4-6.5 with memory
<b>Zoom ratio</b>	1.42 Motorized zoom and focus with memory
<b>Focal length</b>	23.95-34.02 mm
<b>Focus Range</b>	Standard: 1.5m – 15m
<b>Weight</b>	2.8 kg
<b>Shipping weight</b>	3.4 kg
<b>Throw Ratio</b>	DMD chip WUXGA 1.12-1.58 :1 WQXGA 1.20-1.70:1 Image size tolerance +/-2%

Créé le : 02 Jun 2020

Les spécifications techniques sont susceptibles d'être modifiées sans préavis. Veuillez consulter les dernières informations disponibles sur [www.barco.com](http://www.barco.com).