



T-20

Module LED d'extérieur, 6 600 cd/m², pas de pixel de 20 mm



SPÉCIFICATIONS TECHNIQUES**T-20**

Pixel pitch	20.0 mm
Brightness	6,000 nits
LED configuration	3x lamp
Pixel density	2,504 LEDs per tile (48x48)
Pixel density	2,504 LEDs per tile (48x48)
Hor. viewing angle	110° (min 50% brightness)
Vert. viewing angle	+15, -45° (min 50% brightness)
Contrast ratio	4,000:1 (at 500 lux)
Lifetime	100,000 hours to 50% of initial brightness
Power consumption	400W/tile (max) 120W average
Operation power voltage	200-240V / 50-60Hz
Tile dimensions	Width: 960mm Height: 960mm Depth: 281.95mm
Tile dimensions	Width: 960mm Height: 960mm Depth: 281.95mm
Tile dimensions	Width: 960mm Height: 960mm Depth: 281.95mm
Tile dimensions	Width: 960mm Height: 960mm Depth: 281.95mm
Weight / Tile	60 kg
IP rating	IP65/54
Processing	16 bit/color
Colors	281 trillion
Refresh rate	800Hz
Foot build-up	Max. 6 tiles high
Truss build-up	Max. 10 tiles high
Link interface	DVI interface (DVI connector)
Max link length	4.5m (with Barco DVI cable)
Interfaces	2x DVI
Max power cascade connection	6 tiles
Serviceability	Back (screwed shader)
Operating temperature	-35 -50°C
Storage temperature	-35 -50°C
Operational humidity	10-99%
Storage humidity	10-99%
Source compatibility	CVBS, YC, YUV, RGB, DVI, SDI, HDSDI (DX-700: and Dual link DVI, Dual link HDSDI)
Operable digitizer	DX-700 (with DVI output card), D320, LEDPRO
Certifications	ETL, CE, FCC, RoHS, CCC, TUV

Crée le : 21 Jan 2018

Les spécifications techniques sont susceptibles d'être modifiées sans préavis. Veuillez consulter les dernières informations disponibles sur www.barco.com.