

# iQ R350

Barco's advanced picture-in-picture LCD projector with SXGA+ resolution and a brightness of 3,500 ANSI lumens



**SPECIFICHE TECNICHE****IQ R350**

<b>Emissione luminosa</b>	3,500 ANSI lumens
<b>Risoluzione</b>	SXGA+ (1400 x 1050)
<b>Uniformità della luminosità</b>	> 95 % for the total screen
<b>Rapporto di contrasto</b>	> 800:1 (full white/full black)
<b>Display</b>	3 active matrix 1.4" diagonal SXGA+ polysilicon LCD panels with Micro Lens Arrays and a resolution of 1400 x 1050 pixels (aspect ratio 4:3). LCD panels are selected for a minimum of pixel defects.
<b>Caratteristiche</b>	<ul style="list-style-type: none"><li>■ AutoImage</li><li>■ Advanced picture-in-picture</li><li>■ Seamless switching with effects</li><li>■ Standard cable basket</li><li>■ Standard light shutter</li><li>■ Advanced digital zoom</li></ul>
<b>PIP (Picture-In-Picture)</b>	Up to 4 sources simultaneously (2 data, 1 video and 1 SDI)
<b>Ingressi</b>	<ul style="list-style-type: none"><li>■ 1x Configurable 5-Wire (BNC) for: Composite Video, S-Video, Component Video, RGBHV, RGBS, RGsB.</li><li>■ 1x Composite Video (BNC) (up to 7 Composite Video's when using all connectors on top input board)</li><li>■ 1x S-Video (4-pin mini-DIN) (up to 3 S-Video's when combining BNC's)</li><li>■ 1x VGA (D15 connector)</li><li>■ 1x DVI (Digital Visual Interface)</li></ul>
<b>Uscite</b>	No output
<b>Comunicazione</b>	1x D9 connectors for RS232 In/Out 1x spherical IR receiver
<b>Compatibilità</b>	<ul style="list-style-type: none"><li>■ All current video sources (PAL, SECAM, NTSC) in Composite, S-VHS, Component or RGB formats</li><li>■ All currently proposed HDTV, extended and improved television standards (1080i, 720p)</li><li>■ All computer graphics formats from VGA, SVGA, XGA, SXGA to UXGA</li><li>■ Most Macintosh computers</li><li>■ Electronic workstations with a resolution up to 1600 x 1200 pixels at 75 Hz</li><li>■ Most computer sources with a pixel clock up to 160 MHz</li><li>■ DVI sources up to SXGA+</li></ul>
<b>Compatibilità sorgente ingresso</b>	1600 x 1200 (max. input)
<b>Dimensioni schermo</b>	From 1-6m / 3-20ft.
<b>Frequenze di scansione</b>	Horizontal 15kHz -110 kHz Vertical 25 Hz -150 Hz
<b>Connessione in rete</b>	Refer to iQ Pro R350
<b>Server per visualizzazione integrato</b>	Refer to iQ Pro R350
<b>Temperatura ambiente</b>	5°C up to 40°C
<b>Lampada</b>	2x 250 Watt UHP lamp, in lamp housing, pre-aligned for max. light output. Typical lifetime: 3000 h/lamp. 3000 hours in Dual Lamp Mode or max. 6000 hours/set in Single Lamp Mode.
<b>Ottiche</b>	Fixed focal length lenses are available with a throw ratio of 0.85:1 (very short throw ratio, specially designed for rear screen on-axis projection) or 7.0:1 (long throw).  Variable focus lenses with a throw distance of 1.3-1.8, 1.9-2.6, 3.0-6.0 times the screen width.(2.5% tolerance)
<b>Spostamento obiettivo</b>	QVD lenses Motorized V shift: -30% +110%  For specific details per lens type: see lens product pages

**SPECIFICHE TECNICHE****IQ R350**

Encoder obiettivo	Not Applicable
ScenergiX	Not Applicable
Elemento centrale DLP™ sigillato	Not Applicable
Filtri polvere	High Quality Microfilter (side removeable)
Livello di rumore	< 37dB
Tensione di alimentazione	90V-255V
Consumo energetico	Max. 520 Watt
Dissipazione alimentazione	Max. 1775 BTU/h
Alimentazione CA	Power factor pre-regulated SMPS, 90-254 VAC / 50-60Hz
Peso	Net weight: Body only 12.9kg / 28.5 lbs. Shipping weight: • without lens: max.17.5 kg / 28.5 lbs. • with lens: max. 20 kg / 44 lbs.
Dimensioni:	Projector body with cable basket: 415 mm (max. W) x 195 mm (max. H) x 565 (max. D) Projector body without cable basket: 415 mm(max. W) x 195 mm (max. H) x 487 (max. D)
Norme di sicurezza	Compliant with UL1950 and EN60950
Interferenza elettromagnetica	Compliant with FCC rules & regulations, part 15 Class B and CE EN55022 Class B

Generato il: 21 Jan 2018

Le informazioni e i dati forniti riguardano l'apparecchiatura descritta. Tuttavia ogni singolo articolo è soggetto a modifiche senza preavviso.<br /> L'ultima versione di questo opuscolo è disponibile all'indirizzo [www.barco.com](http://www.barco.com).