

FLDX 1,2-1,7:1 (EN63)

WUXGA 1,12-1,58:1 WQXGA/4K 1,20-1,70:1 F80: 1,59-2,24:1 (WQXGA/4K UHD) (F80 richiede l'adattatore per obiettivo FLD/FLD+)



SPECIFICHE TECNICHE**FLDX 1,2-1,7:1 (EN63)**

Platforms	For F35, FL40, F70, F80* and F90 projector series *requires lens adapter R98014421. F80 specific throw ratio: 1.59 -2.24 : 1 (WQXGA/4K UHD)
Working F/#	F 2.4-2.7 Motorized Iris F# 2.4-6.5 with memory
Zoom ratio	1.42 Motorized zoom and focus with memory
Focal length	23.95-34.02 mm
Focus Range	Standard: 1.5m – 15m
Weight	2.8 kg
Shipping weight	3.4 kg
Throw Ratio	DMD chip WUXGA 1.12-1.58 :1 WQXGA 1.20-1.70:1 Image size tolerance +/-2%

Generato il: 02 Jun 2020

Le informazioni e i dati forniti riguardano l'apparecchiatura descritta. Tuttavia ogni singolo articolo è soggetto a modifiche senza preavviso.
 L'ultima versione di questo opuscolo è disponibile all'indirizzo www.barco.com.