

iQ Pro G210L

Barco's Network Centric LCD projector with XGA resolution and an amazing brightness level of 2,200 ANSI lumens.



SPECIFICHE TECNICHE**IQ PRO G210L**

Light output	2,200 ANSI lumen
Brightness uniformity	>95% for the total screen
Contrast ratio	>800:1 (full white/full black)
LCD panels	3 active matrix 1.4" diagonal XGA polysilicon LCD panels with Micro Lens Arrays and a resolution of 1024 x 768 pixels (aspect ratio 4:3).
Resolution	1024 x 768 (native)
Networking	<p>iQ Pro Server Specifications: -Processing Power: Pentium III socket with 1,2 Gigahertz Tualatin Celeron processor -Memory: 256 MB RAM -Storage: 40 GB hard disk -Video memory up to 64 MB -Inputs and outputs</p> <ul style="list-style-type: none">■ PCMCIA slot for Wireless LAN cards, memory cards, Bluetooth, input extensions ... RJ45connector for Ethernet (10Mb/s) and Fast Ethernet (100Mb/s) 4 USB connectors Audio: 3,5 mm jacks for Microphone in, Line in and Line out
Features	· Advanced picture-in-picture · Seamless switching with effects · Standard cable basket · Standard light shutter · Advanced digital zoom
Compatibility	<p>The iQ Pro G210L is compatible with:</p> <ul style="list-style-type: none">■ All current video sources (PAL,SECAM, NTSC) in Composite, S-VHS, Component or RGB formats All currently proposed HDTV, extended and improved television standards (1080i, 720p) All computer graphics formats from VGA, SVGA, XGA, SXGA to UXGA Most Macintosh computers Electronic workstations with a resolution up to 1600 x 1200 pixels at 75 Hz Most computer sources with a pixel clock up to 160 MHz DVI sources up to SXGA
Screen size	from 1-6m / 3-20ft.
Inputs	<ul style="list-style-type: none">• 1x Configurable 5-Wire (BNC) for: Composite Video, S-Video, Component Video , RGBHV, RGBS, RGsB.• 1x Composite Video (BNC) (up to 7 Composite Video's when using all connectors on top input board)• 1x S-Video (4-pin mini-DIN) (up to 3 S-Video's when combining BNC's)• 1x VGA (D15 connector)• 1x DVI (Digital Visual Interface)
Lamp	<p>2x 120 Watt UHP lamp, in lamp housing Typical lifetime: 6000 h/lamp. 6000 hours in Dual Lamp Mode or max. 12000 hours/set in Single Lamp Mode.</p>

SPECIFICHE TECNICHE**IQ PRO G210L**

Lenses	Fixed focal length lenses are available with a throw ratio of 0.85:1 (very short throw ratio, specially designed for rear screen on-axis projection) or 7.0:1 (long throw). Variable focus lenses with a throw distance of 1.3-1.8,1.9-2.6, 3.0-6.0 times the screen width
Scan Frequencies	Horizontal 15 kHz -110 kHz Vertical 25 Hz -150 Hz
Lens Shift	QVD Lenses Motorized V shift: -30% +110% For specific details per lens type: see lens product pages
Dimensions (WxLxH)	Projector body with cable basket: 415 mm (Max W) x 195 mm (Max H) x 565 mm (Max D) Projector body without cable basket: 415 mm (Max W) x 195 mm (Max H) x 487 mm (Max D)
Weight	Projector body with cable basket: 415 mm (Max W) x 195 mm (Max H) x 565 mm (Max D) Projector body without cable basket: 415 mm (Max W) x 195 mm (Max H) x 487 mm (Max D)
Communication	<ul style="list-style-type: none">• 1x D9 connectors for RS232 In/Out• 1x spherical IR receiver
AC power	Power factor pre-regulated SMPS, 90-254 VAC / 50-60Hz
Noise Level	
Power consumption	Max 380 Watt
Power Dissipation	Max 1297 BTU/h
Safety Regulations	Compliant with UL1950 and EN60950
Electromagnetic Interference	Barco's iQ Pro G210L complies with FCC rules & regulations, part 15 Class B and CE EN55022 Class B
Seamless Switching	standard

Generato il: 21 Jan 2018

Le informazioni e i dati forniti riguardano l'apparecchiatura descritta. Tuttavia ogni singolo articolo è soggetto a modifiche senza preavviso.
 L'ultima versione di questo opuscolo è disponibile all'indirizzo www.barco.com.