

# iQ Pro G210L

Barco's Network Centric LCD projector with XGA resolution and an amazing brightness level of 2,200 ANSI lumens.



**SPECIFICHE TECNICHE****IQ PRO G210L**

---

<b>Emissione luminosa</b>	2,200 ANSI lumen
<b>Uniformità della luminosità</b>	>95% for the total screen
<b>Rapporto di contrasto</b>	>800:1 (full white/full black)
<b>Pannelli LCD</b>	3 active matrix 1.4" diagonal XGA polysilicon LCD panels with Micro Lens Arrays and a resolution of 1024 x 768 pixels (aspect ratio 4:3).
<b>Risoluzione</b>	1024 x 768 (native)
<b>Connessione in rete</b>	iQ Pro Server Specifications: -Processing Power: Pentium III socket with 1,2 Gigahertz Tualatin Celeron processor -Memory: 256 MB RAM -Storage: 40 GB hard disk -Video memory up to 64 MB -Inputs and outputs <ul style="list-style-type: none"><li>■ PCMCIA slot for Wireless LAN cards, memory cards, Bluetooth, input extensions ... RJ45connector for Ethernet (10Mb/s) and Fast Ethernet (100Mb/s) 4 USB connectors Audio: 3,5 mm jacks for Microphone in, Line in and Line out</li></ul>
<b>Caratteristiche</b>	· Advanced picture-in-picture · Seamless switching with effects · Standard cable basket · Standard light shutter · Advanced digital zoom
<b>Compatibilità</b>	The iQ Pro G210L is compatible with: <ul style="list-style-type: none"><li>■ All current video sources (PAL,SECAM, NTSC) in Composite, S-VHS, Component or RGB formats All currently proposed HDTV, extended and improved television standards (1080i, 720p) All computer graphics formats from VGA, SVGA, XGA, SXGA to UXGA Most Macintosh computers Electronic workstations with a resolution up to 1600 x 1200 pixels at 75 Hz Most computer sources with a pixel clock up to 160 MHz DVI sources up to SXGA</li></ul>
<b>Dimensioni schermo</b>	from 1-6m / 3-20ft.
<b>Ingressi</b>	<ul style="list-style-type: none"><li>• 1x Configurable 5-Wire (BNC) for: Composite Video, S-Video, Component Video , RGBHV, RGBS, RGsB.</li><li>• 1x Composite Video (BNC) (up to 7 Composite Video's when using all connectors on top input board)</li><li>• 1x S-Video (4-pin mini-DIN) (up to 3 S-Video's when combining BNC's)</li><li>• 1x VGA (D15 connector)</li><li>• 1x DVI (Digital Visual Interface)</li></ul>
<b>Lampada</b>	2x 120 Watt UHP lamp, in lamp housing Typical lifetime: 6000 h/lamp. 6000 hours in Dual Lamp Mode or max. 12000 hours/set in Single Lamp Mode.

---

**SPECIFICHE TECNICHE****IQ PRO G210L**

<b>Ottiche</b>	Fixed focal length lenses are available with a throw ratio of 0.85:1 (very short throw ratio, specially designed for rear screen on-axis projection) or 7.0:1 (long throw).  Variable focus lenses with a throw distance of 1.3-1.8, 1.9-2.6, 3.0-6.0 times the screen width
<b>Frequenze di scansione</b>	Horizontal 15 kHz -110 kHz Vertical 25 Hz -150 Hz
<b>Spostamento obiettivo</b>	QVD Lenses Motorized V shift: -30% +110%  For specific details per lens type: see lens product pages
<b>Dimensioni (PXLXA)</b>	Projector body with cable basket: 415 mm (Max W) x 195 mm (Max H) x 565 mm (Max D) Projector body without cable basket: 415 mm (Max W) x 195 mm (Max H) x 487 mm (Max D)
<b>Peso</b>	Projector body with cable basket: 415 mm (Max W) x 195 mm (Max H) x 565 mm (Max D) Projector body without cable basket: 415 mm (Max W) x 195 mm (Max H) x 487 mm (Max D)
<b>Comunicazione</b>	<ul style="list-style-type: none"><li>• 1x D9 connectors for RS232 In/Out</li><li>• 1x spherical IR receiver</li></ul>
<b>Alimentazione CA</b>	Power factor pre-regulated SMPS, 90-254 VAC / 50-60Hz
<b>Livello di rumore</b>	
<b>Consumo energetico</b>	Max 380 Watt
<b>Dissipazione alimentazione</b>	Max 1297 BTU/h
<b>Norme di sicurezza</b>	Compliant with UL1950 and EN60950
<b>Interferenza elettromagnetica</b>	Barco's iQ Pro G210L complies with FCC rules & regulations, part 15 Class B and CE EN55022 Class B
<b>Commutazione continua</b>	standard

Generato il: 21 Jan 2018

Le informazioni e i dati forniti riguardano l'apparecchiatura descritta. Tuttavia ogni singolo articolo è soggetto a modifiche senza preavviso.<br /> L'ultima versione di questo opuscolo è disponibile all'indirizzo [www.barco.com](http://www.barco.com).