

E2 Jr

Cost-effective Event Master processor



- **Easy and reliable show setup and production**
- **Market-valued 4K performance**
- **Future-proof upgradability to the full E2 system**

Bringing the same performance and features as the E2, the E2 Jr model is ideally suited for applications that do not require the full capacity of the E2. Offering 16 inputs, 8 outputs, and 8 mixers (or 16 single layers), the E2 Jr features the same 4 RU form factor as its bigger E2 brother.

Easy upgrading

Thanks to its modular design E2 grows with your shows so you can easily upgrade the E2 Jr to a fully loaded E2 system at any time. You can simply purchase and install additional cards into your system. This modularity also ensures great serviceability, as users can easily swap a specific input or output card in the case of damage, without needing to ship or replace the entire box.

Designed for life on the road

Designed for the live event industry, the rugged E2 Jr features a steel chassis that's able to withstand the challenging conditions of life on the road. What's more, it offers screen control in a compact form factor of only four rack units, which makes it easy to ship and install. And thanks to its modular cards and dual redundant power supplies, the E2 Jr is extremely reliable and easy to service in the field.

TECHNISCHE SPECIFICATIES**E2 JR**

Model	NGS-4U-V2
Live-effectcanvas	Up to 10 Megapixels PVW/PGM 20 Megapixels PGM only 40 Megapixels @30p and PGM only
Video-ingangen	16 inputs via 4 input cards (Event Master series cards) <ul style="list-style-type: none">Up to 4 x 4K inputs - each input card supports up to 4K@60p4 x SD/HD/3G SDI6 x HDMI 1.4a (297 Mpix/sec max)6 x DisplayPort 1.1 (330 Mpix/sec max)
Video-uitgangen	10 outputs via 3 output cards (Event Master series cards) <ul style="list-style-type: none">Up to 2 x 4K outputs - each output card supports up to 4K@60 p4 x SD/HD/3G SDI4 x HDMI 1.4a (297 Mpix/sec max)2 x HDMI 1.4a for Multiviewer (297 Mpix/sec max)
Genlock	Analog reference input/loop on BNC connectors; bi-level and blackburst at SD and tri-level at HD S3D Sync: 4x input Din connector, 2x output Din connector
Programma-uitvoer	Up to 8 program outputs configurable as single screens or tiled/blended widescreens <ul style="list-style-type: none">Configurable for up to 8X 2048X1200@60 max or up to 2 x 4096x2400@60 maxIndependent edge blending/feathering control for all four sides
Aux-uitgangen met schaalverdeling	User definable from 4 x 2048x1200@60 to 1 x 4K@60 All outputs can be defined as Aux destinations for a total of 8 Aux outputs Output color correction
Mixers	<ul style="list-style-type: none">Native resolution background mixer per output screenIndependent layer transitions or full Preview/Program transitionFlexible layer allocation - up to 8 mixable or 16 single scalable PIP/key layers assignable to Program output screens
Geheugenruimte voor foto's	Up to 100 HD stills available in background, Aux or PIP
Laageffecten	<ul style="list-style-type: none">Borders (hard, soft, halo) and drop shadowsColor effectsStrobe, H&V flipLuma keyPIP moves via Keyframes
Multiviewer	<ul style="list-style-type: none">Flexible user-definable layoutsMonitor all Inputs and Outputs, including Preview and AuxTwo outputsDedicated hardware same E2 Event Master Processors
Uitbreidbaarheid	Linking is available as an upgrade option
HDCP	HDCP compliant
Controle	<ul style="list-style-type: none">Event Master screen management software for PC or MACEthernet RJ-45, 1000/100/10 Mbps autosense
Onderhoudsgemak	<ul style="list-style-type: none">Field-serviceable I/O and processing cards (not hot-swappable)Hot-swappable dual-redundant power supplies
Geluidsniveau	Max 52.9 dB avg. Fans at 100%. Fan speed is software managed based on operating temperature. Reference ISO 7779
Afmetingen	<ul style="list-style-type: none">Height: 17.8 cm (7.0 in) - 4 RU rack mountWidth: 43.2 cm (17 in) without chassis handles, 48.3 cm (19 in) with chassis handles attachedDepth: 56.9 cm (22.4 in) from front panel to rear panel, 62.2 cm (24.5 in) overall
Gewicht	27.8 kg / 61 lbs
Vermogen	<ul style="list-style-type: none">Input power: 100-240Vac, 50/60Hz, 12-5A (x2), 700WDual-redundant, hot-swappable power supplies
Garantie	3 years parts and labor
Omgevingstemperatuur	0-40° C / 32-104 F
Omgevingsvochtigheid	0-95% non-condensing

Last updated: 13 Mar 2023Technical specifications are subject to change without prior notice. Please check www.barco.com for the latest information.