

RGB Laser ODL-821

80" laser-lit rear-projection video walls for 24/7 control rooms



- **1.5x more brightness than mainstream 80" LED-lit rear-projection video walls**
- **25% less power consumption at higher brightness levels**
- **More than 11 years of uninterrupted operation in 24/7 mode**
- **Unmatched colors, focus, and contrast levels**
- **Lower price/m2 (compared to 70" cubes)**
- **Silent like never before ('library' noise level)**
- **Redundancy of critical components for ultimate peace of mind**
- **50% setup-time reduction (motorized 7-axis alignment)**

Powered with the latest laser technology, Barco's RGB laser rear-projection video walls delivers unseen brightness levels and vibrant colors, while offering a very low total cost of ownership (TCO). With its 10th generation of rear-projection video walls, Barco again raises the bar for critical infrastructure visualization.

Providing 1.5x more brightness than mainstream 80" LED-lit rear-projection video walls, the RGB Laser series removes all brightness issues of earlier video walls. The high luminance allows operation under daylight conditions, so control rooms can finally light up - which improves operator working conditions! Adding vibrant colors to this mix (making all nuances clearly distinguishable), ensures that nothing is wrongly interpreted and situational awareness is enriched. What's more, using 80" cubes results in a lower price per square meter and less seams for the large video wall.

Over 11 years of uninterrupted 24/7 operations

With the RGB laser for 24/7 control rooms series, Barco takes another giant leap forward in terms of reliability. With a light source lifetime of at least 125,000 hours in both normal and eco-mode, and redundancy of all critical components (including power supply, inputs, and laser drivers), nothing is left to chance when it comes to uptime. Unlike technology used by others and for non-24/7 environments, Barco's RGB laser display series doesn't need a rotating color wheel to operate. Since each color can be uniquely controlled and is not dependent on the segment of a color wheel, it provides color control like never before and eliminates color breakup.

Automatic calibration and alignment

The engine of Barco's RGB laser for 24/7 control rooms is fully motorized. Installers and maintenance staff will never need to open up the individual modules to perfectly align the individual cubes of the video wall. Using a web interface, the video wall can be remotely aligned by a single technician - including keystone correction. Combined with the Sense X automatic calibration system, which continuously measures and adjusts brightness and color levels over the complete video wall, users are sure the complete canvas is perfectly balanced at any time.

TECHNISCHE SPECIFICATIES**RGB LASER ODL-821**

| | | | | |
|------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------|-----------------------------|-----------------|
| Resolutie | Full HD (1920 x 1080 pixels) | | | |
| Schermhelderheid (bij native kleurenspectrum) | Mode | Brightness | Light source lifetime (hrs) | Power usage (W) |
| | Boost | 500 cd/m ² | 60,000 | 260 |
| | Normal | 390 cd/m ² | 125,000 | 200 |
| | Eco | 195 cd/m ² | 125,000 | 120 |
| Contrast op scherm | 1800:1 | | | |
| Schermb | BBP Horizontal half gain viewing angle: 30° Vertical half gain viewing angle: 30° | | | |
| Kleur | Up to 170% REC709 color triangle | | | |
| Weergavetechnologie | Rear projection DLP (rear access only) | | | |
| Wit punt | Customized white points | | | |
| Helderheidsuniformiteit | Typ. >95% ANSI 9 Typ. >90% ANSI 13 | | | |
| Ruimte tussen schermen | Hor: 1.2 mm, Vert. 0.8 mm (@ 25°C) | | | |
| Kleurstabiliteit | Sense X automatic calibration | | | |
| Afmetingen | <ul style="list-style-type: none"> • Diagonal: 80" (Approx.) • Width: 1,760 mm 69.29" • Height: 990 mm 38.97" • Depth: 730 mm 28.74" • Weight: Projection Module: 65.5 Kg 144.4 lbs • Weight: Support frame (1m): 42 Kg 92.5 lbs | | | |
| Lichtbron | RGB lasers illumination (Lasers Class 1 RG2) | | | |
| Redundantie | Redundant laser banks with redundant power supply drivers, input signal & external power supply | | | |
| Levensduur lichtbron | > 125,000 hrs in both Normal and Eco mode | | | |
| Geluidsniveau | Less than 20 dB (measured from 3 meters in front) | | | |
| Gebruiksomstandigheden | 10°C-40°C 50°F-104°F Up to 80% humidity (non-condensing) | | | |
| Ingangsspanning (wisselstroom) | 100 – 240 VAC, 50-60Hz | | | |
| Vermogen | 120W (eco) 200W (normal) | | | |
| Warmtedissipatie | 390 BTU/h (eco) 680 BTU/h (typ) 860 BTU/h (max) | | | |
| Connectiviteit | 2x DP1.2 inputs & 1x output (4K@60Hz) 2x HDMI 2.0 inputs (4K@60Hz) 2x USB ports (only for power) 2x Ethernet ports | | | |
| Signaalverwerking | Loop through Cropping, scaling with wall configuration | | | |
| Directe Ethernet-toegang | Built in web server | | | |
| Grafische gebruikersinterface | All settings and operational parameters | | | |
| Integratie met apparatuur van derden | WEB service API | | | |
| Garantie | 2 years | | | |

Last updated: 19 Nov 2021

Technical specifications are subject to change without prior notice. Please check www.barco.com for the latest information.