

FLDX 1.7- 2.5: 1 (EN61)



TECHNISCHE SPECIFICATIES**FLDX 1.7- 2.5: 1 (EN61)**

Platforms	For F35, FL40, F70, F80* and F90 projector series *requires lens adapter R9801442. F80 specific throw ratio: 2.38 -3.51 : 1 (WQXGA/4K UHD)
Working F/#	F 2.1-2.5 Motorized Iris F# 2.1-6.5 with memory
Zoom ratio	1.47 Motorized zoom and focus with memory
Focal length	33.7-49.54 mm
Focus Range	Standard: 1.5m – 15m
Weight	2.6 kg
Shipping weight	3.1 kg
Throw Ratio	DMD chip WUXGA 1.58-2.33 :1 WQXGA 1.70-2.50 :1 Image size tolerance +/-2%

Last updated: 02 Sep 2020

Technical specifications are subject to change without prior notice. Please check www.barco.com for the latest information.