

# MXRT-2700

2GB small form factor display controller



- **Optimal performance**
- **Reliable longevity**
- **Guaranteed workflow support**

## Your journey in improved workflow begins here

The Barco MXRT-2700 graphics card delivers the essential workflow features, quality, and support to ensure radiologists can perform at their full potential. With 2GB of graphics memory driving three DisplayPort 1.4 outputs, it is the ideal solution for those looking for a cost-effective, reliable professional graphics card that can fit almost any workstation including small, power constrained systems.

Whether driving diagnostic, clinical, or auxiliary displays, the MXRT-2700 is fully functional as a main display controller or complementing a more advanced multi-head configuration. Key features include 3 ports to cover most basic display configurations, ample memory for PACS image loading, and low power requirements compatible with entry-level workstations in a small form factor for when compact size really matters.

Please consult your Barco representative or distributor in your country or territory to confirm availability. A reference to any product or service on this site does not imply that such product is or will be available in your location.

- 2GB GDDR5 display memory
- 48 GB/s memory bandwidth
- 64-bit memory interface
- 1 DisplayPort 1.4 & 2 mini DisplayPorts 1.4 (2 mDP to DP locking adapters included)
- Maximum power consumption: <40W

**TECHNISCHE SPECIFICATIES****MXRT-2700**

Buscompatibiliteit	PCIe Gen3 x8
Energieverbruik	< 35W
Vormgeving	168 mm (L) x 60mm (H) single wide PCIe slot
Besturingssysteem	Windows 7 (64-bit), Windows 10 (64-bit)
Platformen	Intel® and AMD architectures
Stroomconnector	None
Grafische versneller	AMD Radeon Pro™
Weergavegeheugen	2GB DDR5
Geheugeninterface	64-bit
Geheugenbandbreedte	48 GB/s
Pixeldiepte	32-bit pixels (10-bit grayscale and 30-bit color)
Elektrische standaard	DisplayPort (DP) v1.4
Direct3D-hardwareondersteuning	Microsoft® DirectX v12, Vulkan® 1.1, Shader Model 5.1
OpenGL-hardwareondersteuning	OpenGL 4.5
Connectoren	(1x) DisplayPort 1.4 (2x) Mini-DisplayPort 1.4
Connectiviteit	Native DisplayPort suggested DisplayPort to Single-link DVI adapter available separately (2x) Mini-DP to DP locking adapters included
Goedkeuringen en conformiteit	FCC Part 15 Class B, CE EN 55032 Limit B, EN 55024, UL-60950-1, BMSI CNS, CISPR-32/24, IEC609050-1, VCCI, CSA C22.2, EU RoHS directive (2011/65/EU), Certificate of Information & Communication Equipment (Republic of Korea)
Bedrijfstemperatuur	0° to 55°C

Last updated: 27 Feb 2023

Technical specifications are subject to change without prior notice. Please check [www.barco.com](http://www.barco.com) for the latest information.