

ClickShare CS-100

Zelfstandig draadloos presentatiesysteem voor kleine vergaderruimtes



- Draadloze verbinding met het centrale scherm
- 1 gebruiker op het scherm
- Delen vanaf laptop, tablet of smartphone
- HDMI-uitgang
- Geleverd met 1 Button

Succesvolle vergaderingen gaan over vertrouwen. Vertrouwen in de ideeën, vertrouwen in de presentaties, maar ook vertrouwen in de techniek van de vergaderruimte. Daarom heeft Barco ClickShare ontwikkeld. Met dit draadloze presentatiesysteem kunnen gebruikers eenvoudigweg delen wat er op hun laptop of mobiel apparaat staat, op het presentatiescherm. Geen kabels, geen instellingen, niet wachten om mee te doen.

Ontdek wat er nieuw is in de laatste ClickShare-update

Delen als basisbehoefte

De CS-100 brengt de ClickShare-ervaring naar kleine vergader- en huddle-ruimten waar het delen van inhoud vanaf een laptop of mobiel apparaat een basisbehoefte is. Iedereen – ook de gasten – kan met één klik verbinding maken en direct delen, zonder dat er een training nodig is. Gebruikers sluiten gewoon een USB-apparaat – de ClickShare Button – aan op hun pc of Mac en klikken op de button om de inhoud van hun laptop op het grote scherm van de vergaderruimte te tonen. Met de ClickShare-apps kunnen gebruikers ook inhoud van hun laptop, mobiele telefoon of tablet delen. Zorg dat de laatste firmware-versie geïnstalleerd is op je basisstation om de beste ervaring te krijgen met de bureaubladapp.

Zelfstandig model

De CS-100 is een zelfstandig model met een HDMI-uitgang, die het mogelijk maakt om tot 8 gebruikers aan te sluiten, waarbij één gebruiker tegelijk deelt. De CS-100 bevat de standaard ClickShare-beveiligingsfuncties, waaronder versleuteling, aanmeldingsbeheer, https en de mogelijkheid om de SSID van het draadloze netwerk van het basisstation te verbergen.

De CS-100 is gemaakt met ISO 27001-gecertificeerde stromen en processen.

Door ClickShare CS-100 toe te voegen aan je vaste vergaderruimte (zoals een Microsoft Teams- of Zoom-ruimte), verbeter je de samenwerking in je Microsoft Teams- en Zoom-vergaderingen. Het brengt de focus van vergaderen terug naar echt samenwerken.

PRODUCT SPECIFICATIONS**CLICKSHARE CS-100**

General specifications	
Operating system	Windows 7/8/8.1/10 32 & 64 bit macOS 10.14/10.15 (Catalina) Android 9 & 10 (ClickShare app) iOS 11, 12 & 13 (ClickShare app)
Video outputs	1x HDMI 1.2
Output resolution	1920x1080 @60Hz
Audio	Via HDMI, analog via Audio Jack 3.5mm
Frame rate	Up to 30 fps*
Number of sources simultaneous on screen	1
Number of simultaneous connections	8
iPad, iPhone and Android compatibility	Sharing of documents, browser, camera for both Android and iOS devices via ClickShare app
Extended desktop	Available for Windows, requires ClickShare Extension Pack.
Authentication protocol	WPA2-PSK in stand-alone mode WPA2-PSK or IEEE 802.1X using the ClickShare Button in network integration mode
Wireless transmission protocol	IEEE 802.11 a/g/n
Reach	Adjustable with signal strength modulation; max. 30m (100 ft) between ClickShare Button and ClickShare Base Unit
Frequency band	2.4 GHz and 5 GHz (DFS channels not supported)
Connections	1x Ethernet LAN 100Mbit 1x (back) + 1x (front) USB Audio analog line out on mini jack socket (3.5mm)
Noise Level	Fanless
Temperature range	Operating: 0°C to +40°C (+32°F to +104°F) Max: 35°C (95°F) at 3000m Storage: -20°C to +60°C (-4°F to +140°F)
Humidity	Storage: 0 to 90% relative humidity, non-condensing Operation: 0 to 85% relative humidity, non-condensing
Anti-theft system	Kensington lock
Certifications	FCC/CE
Warranty	3 years standard
Google Cast Support	Google Cast not supported
*Note	*In optimal WiFi conditions with minimal WiFi interference and as measured during our quality validation. Check Network Deployment Guide for more info on WiFi optimisation and ideal configuration depending on your network environment.

ClickShare Base Unit dimensions

Weight	600g / 1.32lbs
Dimensions (HxWxD)	205mm x 115mm x 45mm (Min.) / 8.1" x 4.5" x 1.8" (Min.)
Power consumption	Operation: 6W (typical) / 18W (max) Standby: 2.6W (ECO standby) / 0.4W (Deep standby)

Last updated: 05 Jul 2021Technical specifications are subject to change without prior notice. Please check www.barco.com for the latest information.