

FLX-60

Large pitch, 60mm transformable LED module



TECHNISCHE SPECIFICATIES**FLX-60**

Brightness	13cd (fully calibrated) -17cd (uncalibrated)
Light output	35 lumens (calibrated) -45 lumens (uncalibrated)
Viewing angle	110° (total half brightness) -140° (usable viewing angle)
Color depth	16-bit/color
LED type	3-in-1 SMD
Socket mount	3 mm bolts or screws through socket
Pixel mount	clip-in 1.5 mm sheet metal or 3 M4 bolts.
Ambient temperature	Max 45° C
Diameter	60 mm
Height	60 mm (incl. socket)
Weight	280g (incl. socket and 300 mm cable)
Protection rating	IP66 (rating when mated)
max. number of pixels on 1 cable	256
Default cable string	16 pixels, 300 mm pitch, interconnectable

Last updated: 26 Nov 2019

Technical specifications are subject to change without prior notice. Please check www.barco.com for the latest information.