

F70-W6

WUXGA laser phosphor projector



- **Durable and robust for 24/7 operation**
- **High brightness**
- **Long lifetime (up to 60,000 hours)**

The F70-W6 laser phosphor projector answers to the simulation and ProAV market's specific requirements - including high robustness, longer lifetime, and laser-sharp image quality. Projectors that do not meet these demands don't last long or require frequent and expensive maintenance.

Fitted with protective metal, Barco's F70 withstands a motion platform's rapid and sudden movements, making it the perfect choice for theme parks. With a lifetime of up to 60,000 hours (depending on the mode of operation), the F70 is one of the most durable projectors on the market and is ready for service in the most demanding environments.

Designed for 24/7 use

The F70 is designed for performance and reliability. Capable of running in any orientation, the F70 projectors offer more installation flexibility. All of Barco's F-series projectors feature the same high-resolution FLD and FLD+ lenses so that you can reuse your lenses.

Brighter, better

With brightness levels of 5,500 lumens, the F70-W6 is one of the brightest single-chip DLP projectors on the market with WUXGA resolution. With the Constant Light Output (CLOTM) functionality, the projector produces constant brightness and color over a long period of time.

TECHNISCHE SPECIFICATIES**F70-W6**

Helderheid	5300 ANSI Lumens minimum 5,800 ANSI Lumens typical
Contrastverhouding	1,800:1 sequential, 50,000:1 dynamic
Infrarood voor nachtkijkers	no
Helderheidsuniformiteit	90%
Beeldverhouding	16:10
Type projector	1DLP laser phosphor
Resolutie	1,920 x 1,200 (WUXGA)
Type lens	FLD-series
Optische lensverschuiving	Vertical up to 134%, depending on lens Horizontal up to 70%, depending on lens Motorized zoom and focus (+ lens memory FLDX lenses) Motorized lens shift (with position memory on all lenses)
Kleurcorrectie	P7 RealColor™
CLU (constante lichtuitvoer)	Yes
Lichtbron	Laser phosphor
Levensduur lichtbron	Up to 60,000 hours, depending on mode of operation
Verzegelde DLP™-kern	Yes
Oriëntatie	360° rotation, no restrictions
3D	Active stereoscopic 3D
Beeldverwerking	Embedded warp & blend engine
Trapeziumcorrectie	Yes
Ingangen	HDSDI 2x DP1.2 2x dual link DVI-I HDBaseT upgradable HDMI2.0 upgradable RJ 45 Ethernet DMX in/out* (upgradable) RS232 in 2x USB 12v out
Invoerresoluties	Including and up to: 1,920 x 1,200 @ 60Hz 2,560 x 1,600 @ 120Hz refresh rates: 24Hz to 120Hz for WQXGA (2560x1600) and 24Hz to 60Hz for 4K/4KUHD (4096 x 2160/ 3860 x 2400)

TECHNISCHE SPECIFICATIES**F70-W6**

Kleurdiepte invoeren	DVI: Native including and up to 1920x1200@120Hz 8 bit RGB. Non-native including and up to 2560x1600@60Hz 8 bit RGB and 3840x2400@50Hz 8 bit RGB DisplayPort: Native including and up to 1920x1200@120Hz 12 bit RGB. Non-native including and up to 2560x1600@120Hz 12 bit RGB and 3840x2400@60Hz 8 bit RGB
Softwaretools	Projector Toolset
Controle	IR, RS232, RJ45
Netwerkverbinding	IR, RS232, RJ45
Voedingsvereisten	100-240V / 50-60Hz
Energieverbruik	743 W nominal, 1100 W maximum
BTU/uur	Max 4,000 BTU/h
Geluidsniveau (standaard bij 25°C/77°F)	36 dB(A)
Bedrijfstemperatuur	10 -40 °C (sea level)
Opslagtemperatuur	-20 to 60 °C
Vochtigheid in bedrijf	20 -80% RH
Vochtigheid bij opslag	10 -90% RH
Afmetingen (B x L x H)	475 x 593 x 286 mm / 18,7 x 23,3 x 11,2 in
Gewicht	37 kg / 81,5 lbs
Standaardaccessoires	Power cord, wireless remote control
Certificeringen	CE, FCC Class A and cNus
Garantie	Limited 5 years parts and labor, extendable

Last updated: 04 Apr 2022

Technical specifications are subject to change without prior notice. Please check www.barco.com for the latest information.