

FLD 1:16 : 1 (EN15)

1.25 : 1 (SX+) / 1.16 : 1 (WUXGA)



Focus range: 1.5 - 15.0 m

Throw ratio

- SX+ 1.25:1
- 1080 / WUXGA 1.16:1

TECHNISCHE SPECIFICATIES**FLD 1:16 : 1 (EN15)**

Working F/#	F 2.1 Motorized Iris F# 2.1-6.5
Zoom ratio	No zoom Motorized focus
Focal length	23.98 mm
Focus Range	Standard: 1.5m – 15m
Custom focus range	Extended focus range is available, please contact sales for details
Weight	2.4 kg
Throw Ratio	DMD chip <ul style="list-style-type: none">■ 1080p/WUXGA 1.16:1■ SXGA+ 1.25:1■ 720p 1.37:1■ XGA 1.71:1
	Image size tolerance +/-5%

Last updated: 13 Nov 2018

Technical specifications are subject to change without prior notice. Please check www.barco.com for the latest information.