

Rugged Remote



- The remote control operation mode enables control of 6000, SLM and ELM Series projectors.
Even when the user menu on screen is switched off during the show, the off screen read out provides you with the necessary information. By connecting the Rugged Remote (wired) to an ELM or SLM lamp house, in the lamp read mode all the specific lamp parameters can be shown.
- Designed with all possible usage situations in mind, this rock solid working partner can also be mounted within a 19" equipment rack. A shoulder strap provides added convenience when climbing trusses.
The handy carrying case contains the following items;
 - *Rugged Remote
 - *Charger
 - *Supplementary mains plugs; UK/US/AUS
 - *SUBD9 male/female adaptor
 - *Lamp communication cable
 - *Shoulder strap
 - *Manual

PRODUCT SPECIFICATIONS**RUGGED REMOTE**

Display	4 lines Liquid Cristal Display fully backlit
Keypad	27 keys fully backlit 5 programmable function keys
Connections	2 way hardwired remote XLR port lamp module info port RS 232/422 port switch RS 422T -RS 422NT -RS232
Communication (baud)	XLR fixed at 57600 bps RS 232/RS 422 (9600 bps, 19200 bps, 38400 bps, 57600 bps, 15200 bps)
Communication range	wired up to 300 m (990 ft)
Address	any number between 0 and 255
Power supply	6x NiCd AA rechargeable batteries (included) or standard batteries 15-30 V DC adaptor 2 charging modes: via external charger or via XLR port of the projector power save mode = automatically switched off after 10 minutes of inactivity
Temperature range	-15 -70° c (5F -158F)
Weight	remote control: 1,3 kg (2,8 lbs) receiver: 0,3 kg (0,6 lbs)

Last updated: 08 Nov 2021

Technical specifications are subject to change without prior notice. Please check www.barco.com for the latest information.