

# S3-4K Jr

Compact and cost-effective Event Master processor



- **Easy and reliable show setup and production**

- **Market-valued 4K performance**

- **Future-proof upgradability to the full S3-4K system**

## **Powerful features, easy operation**

- Modular card-based design
- Easy set-up with the cross-platform Event Master Toolset, providing a step-by-step approach to system configuration
- Serviceable in the field and ready for future signal interfaces via the modular Event Master cards
- Dual, redundant power supplies for maximum peace of mind (optional)
- Widescreen blending support

**TECHNISCHE SPECIFICATIES****S3-4K JR**

<b>Model</b>	NGS-3U
<b>Live-effectencanvas</b>	10 Megapixels PVW/PGM 20 Megapixels PGM only
<b>Video-ingangen</b>	8 HD inputs via 2 input cards (Event Master series cards) <ul style="list-style-type: none"><li>■ Up to 2x 4K inputs - each input card supports up to 4K@60p</li><li>■ 4x SD/HD/3G SDI</li><li>■ 2x HDMI 1.4a (297 MHz)</li><li>■ 2x DisplayPort 1.1 (300 MHz)</li></ul>
<b>Video-uitgangen</b>	8 HD outputs via 2 output cards (Event Master Series Cards) <ul style="list-style-type: none"><li>■ Up to 1x 4K outputs - each output card supports up to 4K@60 p</li><li>■ 4x HDMI 1.4a (297 MHz)</li><li>■ 2x HDMI 1.4a for Multiviewer (297 MHz max) or 4x HDMI 1.4a when used as standard output card</li></ul>
<b>Genlock</b>	Analog reference input/loop on BNC connectors; bi-level and blackburst at SD and tri-level at HD S3D Sync: 4x input Din connector, 2x output Din connector
<b>Programma-uitvoer</b>	4 program outputs configurable as single screens or tiled/blended widescreens Configurable from 4x 2048x1200@60 max to 1x 4096x2400@60 max Independent edge blending/feathering control for all four sides
<b>Aux-uitgangen met schaalverdeling</b>	User-definable from 4x 2048x1200@60 to 1x 4K@60 All outputs can be defined as Aux destinations for a total of 8 Aux outputs Output color correction
<b>Mixers</b>	<ul style="list-style-type: none"><li>■ Native resolution background mixer per output screen</li><li>■ Independent layer transitions or full Preview/Program transition</li><li>■ Flexible layer allocation – 2 mixable or 4 single scalable PIP/key layers assignable to any Program output screen</li></ul>
<b>Geheugenruimte voor foto's</b>	Up to 100 HD or 25 UHD, depending on the import file size.
<b>Laaeffecten</b>	<ul style="list-style-type: none"><li>■ Borders (hard, soft, halo) and drop shadows</li><li>■ Color effects</li><li>■ Strobe, H&amp;V flip</li><li>■ Luma, chroma and Cut/Fill keys (not all modes support keying)</li><li>■ PIP moves via Keyframes</li></ul>
<b>Multiviewer</b>	<ul style="list-style-type: none"><li>■ Flexible user-definable layouts</li><li>■ Monitor all Inputs and Outputs, including Preview and Aux</li><li>■ Two outputs</li><li>■ Dedicated hardware same as E2 Event Master Processor</li></ul>
<b>Uitbreidbaarheid</b>	Linking is available as an upgrade option
<b>HDCP</b>	HDCP compliance determined by installed cards
<b>Controle</b>	<ul style="list-style-type: none"><li>■ Event Master screen management software for PC or Mac</li><li>■ Event Master Controllers</li><li>■ WebUI</li><li>■ Ethernet RJ-45, 1000/100/10 Mbps autosense</li></ul>
<b>Onderhoudsgemak</b>	<ul style="list-style-type: none"><li>■ Field-serviceable I/O and processing cards (not hot-swappable)</li><li>■ Hot-swappable dual-redundant power supplies</li></ul>
<b>Geluidsniveau</b>	Max 51.3 dB avg. Fans at 100%. Fan speed is software-managed based on operating temperature. Reference ISO 7779
<b>Afmetingen</b>	<ul style="list-style-type: none"><li>■ Height: 13.26 cm / 5.22' 3 RU rack mount units</li><li>■ Width: 43.2 cm / 17" without chassis handles, 48.3 cm / 19" with chassis handles attached</li><li>■ Depth: 54 cm / 21.33" overall</li></ul>
<b>Gewicht</b>	21.3 kg / 47 lbs
<b>Vermogen</b>	Input power: 100-240 VAC 50/60Hz 700W Ships with single power supply. Optional Dual-redundant, hot-swappable power supplies available as upgrade.
<b>Omgevingstemperatuur</b>	0-40° C / 32-104 F
<b>Omgevingsvochtigheid</b>	0-95% non-condensing (non-operating) 0-85% non-condensing (operational)
<b>Garantie</b>	3 years parts and labor

**Last updated: 05 May 2022**Technical specifications are subject to change without prior notice. Please check [www.barco.com](http://www.barco.com) for the latest information.