

# FLD lens (1.24 - 1.6 : 1) EN13 (optimized for WUXGA)



- WUXGA = 1.24 - 1.60 : 1 (F70 W, F90 W)
- 1080p = 1.24 - 1.60 : 1
- SXGA = 1.34 - 1.73 : 1
- 720p = 1.47 - 1.89 : 1
- XGA = 1.84 - 2.37 : 1

**PRODUCT SPECIFICATIONS****FLD LENS (1.24 - 1.6 : 1) EN13 (OPTIMIZED FOR WUXGA RESOLUTION)**

---

<b>Working F/#</b>	F 2.1-2.22 Motorized Iris F# 2.1-6.5
<b>Zoom ratio</b>	1.3 Motorized zoom and focus
<b>Focal length</b>	25.59-33.24 mm
<b>Focus Range</b>	Standard: 1.0m – 15m
<b>Custom focus range</b>	Extended focus range is available, please contact sales for details
<b>Weight</b>	2.6 kg
<b>Throw Ratio</b>	DMD chip <ul style="list-style-type: none"><li>■ 1080p/WUXGA 1.24-1.6:1</li><li>■ SXGA+ 1.34-1.74:1</li><li>■ 720p 1.46-1.9:1</li><li>■ XGA 1.83-2.37:1</li></ul>

---

Image size tolerance +/-5%

**Last updated: 24 Feb 2021**

Technical specifications are subject to change without prior notice. Please check [www.barco.com](http://www.barco.com) for the latest information.