

FLD 1.24 - 1.6 : 1 (EN13)

1.34 - 1.74 : 1 (SX+) / 1.24 - 1.6 : 1 (WUXGA)



Focus range: 1.0 - 15.0 m

Throw ratio:

- SX+ 1.34-1.74:1
- 1080 / WUXGA 1.24-1.60:1

TECHNISCHE SPECIFICATIES**FLD 1.24 - 1.6 : 1 (EN13)**

Working F/#	F 2.1-2.22 Motorized Iris F# 2.1-6.5
Zoom ratio	1.3 Motorized zoom and focus
Focal length	25.59-33.24 mm
Focus Range	Standard: 1.0m – 15m
Custom focus range	Extended focus range is available, please contact sales for details
Weight	2.6 kg
Throw Ratio	DMD chip <ul style="list-style-type: none">■ 1080p/WUXGA 1.24-1.6:1■ SXGA+ 1.34-1.74:1■ 720p 1.46-1.9:1■ XGA 1.83-2.37:1
	Image size tolerance +/-5%

Last updated: 13 Nov 2018

Technical specifications are subject to change without prior notice. Please check www.barco.com for the latest information.