

TruePix TP0.9-Q

0.9 mm pixel pitch, high-res indoor LED display for mid-brightness applications



- **Smart engineering guarantees truly seamless outcomes**
- **Smooth and efficient operations, 24/7**
- **Superb color accuracy, under all lighting conditions**
- **Reduced ecological footprint**
- **5 years of dedicated service and support**

TruePix TP0.9-Q is Barco's new flagship indoor high-resolution LED platform. The 27.5" inch tiles, with a 16:9 aspect ratio, have a pixel pitch of only 0.9 mm. TruePix is designed for control room, corporate and broadcast visualization applications and supports both environments exposed to ambient light and controlled lighting environments.

Truly seamless outcomes

TruePix sets a new standard for the LED video wall experience based on decades of experience. The solution brings content to life as intended and ensures predictable, truly seamless outcomes, by combining smart engineering and Infinipix® Gen2, the next generation of Infinipix®. Smooth and efficient operations are guaranteed 24/7, next to full peace of mind.

Barco TruePix' smart engineering introduces a unique mechanical concept for risk-free and precise installations, eliminating visual distortion. This unmatched seamlessness and flatness are achieved through guided module placement and self-leveling mounts. The next generation of Barco's proprietary Infinipix® processing – Infinipix® Gen2 – guarantees full image integrity at any brightness level, together with superb color accuracy. It flexibly and automatically supports any content need while reducing eye fatigue.

Peace of mind at any time

Smooth and efficient operations are guaranteed 24/7 through uninterrupted data flows. Users can reduce the carbon footprint by using the EcoPower standby mode. 5 years of dedicated service and support (ensuring a uniform viewing experience) and remote cloud-based video wall management, allow for peace of mind during the entire product lifetime.

TECHNISCHE SPECIFICATIES**TRUEPIX TP0.9-Q**

Pixelpitch	0.953
Pixel per module	640x360 (HxV)
Led-levensduur	100,000h (video -50% brightness)
Helderheid	>600 nit
Interne verwerking	23 bit
Kleurdiepte	16 bit (281 trillion colors)
Shaders	No
Controle	Infinipix® Gen2
Vernieuwingsnelheid	3,840 Hz
Framesnelheid	24 / 25 / 29.97 / 30 / 47.95 / 48 / 50 / 59.94 / 60 / 100 / 119.88 / 120 / 144 Hz
3D	3D supported
Hor. kijkhoek	160° +/-5°
Vert. kijkhoek	160° +/-5°
Helderheidsuniformiteit	>98%
Dimmen	0-100%
Contrast	TBC
Energieverbruik	775 W/m ² (max) 273 W/m ² (typ)
Warmte-dissipatie	2,643 BTU/h/m ² (max) 1,306 BTU/h/m ² (typ)
Netspanning bij gebruik	100-240V 50/60Hz
Bedrijfstemperatuur	-10°C to +40°C / 14°F to 104°F
Operationele vochtigheid	10 -80%
IP-classificatie	IP30
Redundantie	Power: Optional Data: Inter-tile and signal loop redundancy embedded / N + N redundancy optional
HDR	HLG / HDR10 supported
Concave kromming	Up to 5° inter tile for standard and camera curved frame
Convexe kromming	Up to 3° inter tile for standard curved frame Convex curving is not applicable for camera curved frame
Afmetingen	(WxHxD) 609.92x343.08x71mm / 24.01"x13.5"x2.80"
Gewicht	8.2kg/tile (single PSU) 8.6 kg/tile (dual PSU)
Onderhoudsgemak	Full front & full back service
Kabelbeheer	No external cabling
Installatie	Self-leveling with surface tolerance compensation
Vervangen Module	Automated parallel motorized extraction
Module placement	Guided module placement
Seam quality	Guaranteed seamless
Vlakheid -vlakliggende kwaliteit	Guaranteed flatness
Ergonomie	SteadyView driver algorithm to reduce eye fatigue
Certificeringen	CE, UL, FCC class A, RoHS, WEEE, REACH, CCC, RCM
Garantie	3 years
SmartCare / EssentialCare service offering	5 years

Last updated: 06 Jul 2022

Technical specifications are subject to change without prior notice. Please check www.barco.com for the latest information.