

F50 1080

Compact 120 Hz, single-chip DLP projector with 1080 resolution



- **Razor-sharp images with vivid colors**
- **Active 3D stereo and high frame rates**
- **Compact and rugged design**

Unmatched image quality

With its cutting-edge optics that deliver razor-sharp images, the F50 displays flawless images with vivid colors, and rich in contrast. Producing low noise levels, it also features RealColor™ color management, Smear Reduction Processing™ and high frame rates. The F50 boasts four different digital input sources and a wide range of expansion modules and high-quality projection lenses.

Key benefits

- Small, compact and ruggedized
- Ultimate reliability and low TCO
- Low operational noise level
- Active 3D stereo
- Smear Reduction Processing™/ 120Hz Refresh Rates / High Frame Rates

TECHNISCHE SPECIFICATIES**F50 1080**

Type projector	Single chip DLP digital projector
Technologie	LVDS DMD™ with DarkChip3™
Resolutie	1920 x 1080 (Full HD)
Helderheid	5,500 ANSI lumens (High Brightness) 2,700 ANSI lumens (VizSim Bright) 2,000 ANSI lumens (VizSim)
Contrastverhouding	up to 5,300:1
Helderheidsuniformiteit	>80%
Beeldverhouding	16:9
Type lens	All pure glass lenses
Lenzen	Ultra Wide Fixed EN53 (0.74:1 @1.65m) Wide Fixed EN52 (0.92:1) Super Wide Zoom EN55 (0.80 -1.08:1) Wide Zoom EN56 (1.06 -1.62:1) Zoom EN51 (1.60-2.21:1) Ultra short throw EN57 (0.28:1)
Optische lensverschuiving	Vertical up to 132%, depending on lens Horizontal up to 54%, depending on lens Motorized lens shift
Kleurcorrectie	RealColor™
Lampen	1 x 350W UHP (dimmbable)
Levensduur lamp	Up to 2,000 hours (Full power), Up to 2,500 hours (Eco mode)
Lampbehuizing, snelle vervanging	Yes
Lampgarantie	500 hours or 90 days
Verzegelde DLPT™-kern	Yes
Oriëntatie	Table -ceiling (360 degrees through lamp axis)
3D	Up to 2,560 x 1,600 @ 120Hz
Ingangen	2x DisplayPort 1.2 (HBR2), 1 x DVI-Dual Link, 1 x HDMI 1.4a, 1 x VGA, 2x 3G-SDI, 1x HDBaseT
Invoerresoluties	2,560 x 1,600 -640 x 480 pixel resolution, RGBHV, RGBS, RGsB, custom formats available, HDTV (1080p, 1080i, 720p), NTSC, PAL, SECAM
Max. pixelklok	Up to 600 Mhz (2,560 x 1,600@120 Hz max) DP 1.2 Up to 330 Mhz Dual link DVI
Softwaretools	SimCAD, Projector Toolset
Controle	IR, RS232, Ethernet, USBA, 2x BNC sync, 1x MiniDIN
Netwerkverbinding	10/100/1000 base-T, RJ-45 connection, RS-232
Voedingsvereisten	100-240V 50-60Hz
Energieverbruik	less than 530W
Operationele omgevingstemperatuur	10 -40 °C /50 -104 °F, 0-3,000m (Storage temperature: -20 -60 °C/-4 -140 °F)
Vochtigheid in bedrijf	20 -80% RH (Storage Conditions: 10 -90% RH)
Dissipatie BTU	max 1,807 BTU/h
Afmetingen (B x L x H)	342 x 306 x 143 mm / 13.46 x 12.05 x 5.63 in
Gewicht	7.5 kg / 16.5 lbs
Standaardaccessoires	Power cord, wireless remote control
Certificeringen	Compliant with FCC, part 15 Class A and CCC, cNus, cUL, UL and CE
Garantie	Limited 3 years parts and labour

Last updated: 24 Aug 2021Technical specifications are subject to change without prior notice. Please check www.barco.com for the latest information.