

DP2K-12C

Compact DLP Barco Alchemy Cinema projector (9,500 lumens)



- **Small footprint, budget-friendly performance**
- **Integrated, DCI-compliant**
- **Combines media server functionalities with Series 3 cinema processing electronics**

The Barco Alchemy DP2K-12C is a compact and fully integrated digital cinema projector, based on Texas Instruments' proven 0.98" DLP Cinema® chip. It ensures a first-class movie experience with consistent picture brightness, rich contrast and vibrant colors. By merging the projector and media server functionalities into one module, the DP2K-12C Barco Alchemy projector is a full-fledged, DCI-compliant projector and media-server solution that includes on-board storage. Reducing the required hardware, it increases simplicity and reliability. The smart projector even detects potential operational errors and warns users if, for instance, a scheduled show is missing assets or KDMs. Great in TMS environments, it operates stand-alone in single-screen applications. Thanks to the embedded Barco Web Commander user interface, shows can be created and scheduled remotely.

Low cost of ownership

Geared with the integrated Barco Alchemy technology that drives operational and maintenance costs down, the DP2K-12C offers superior image processing, DCI image quality and ultimate reliability at a low TCO.

Easy operation and maintenance

The DP2K-12C comes with the 'Barco Web Commander' screen management system featuring an intuitive user interface. The projector detects potential operational errors and warns users if, for instance, a scheduled show is missing assets or KDMs. It also has an easy-to-use, fully modular architecture for simple serviceability and higher uptime.

The DP2K-12C projector is also available in a package with a third-party media server and it can be ordered without the Barco Alchemy module as well.



Unique benefits of Barco Alchemy technology

- Combines media server functionalities with cinema processing electronics
- Fewer boxes lead to more reliability and ease-of-use
- Simple operation thanks to intuitive 'Barco Web Commander' user interface
- Easy upgrading of Series 2 projectors with Barco Alchemy module
- Budget-friendly solution with minimal cost of ownership thanks to integrated Barco Alchemy technology, re-usable filters, low maintenance, etc.
- Includes storage
- Maximum ease-of-use through intuitive 'Barco Web Commander' screen management system, running via a web browser
- Barco Communicator for simple configuration and updates of all modules in the projector
- Consistent image quality and brightness thanks to the proprietary sealed engine and advanced DMD cooling
- Easy installation and maintenance thanks to proven modular design and shared components with the other Barco DP2K B-series projectors

TECHNISCHE SPECIFICATIES**DP2K-12C**

Digital MicroMirror Device™	3 x 0.98" DC2K dark metal devices
Native resolutie	2,048 x 1,080 pixels
Behuizing	Hermetically sealed DMDs and optical assembly
Lamp	1.2kW -2kW
Contrastverhouding	2000:1
Lichtuitvoer	9,500 lumens
Schermafmaat	Up to 12m / 39ft wide (screen gain 1.2 @ 14ft)
Primelenszenen	1.2 -1.8 1.4 -2.05 1.6 -2.5 1.95 -3.2 2.4 -3.9
I/O-controle	3x Ethernet 8x GPIO (DB 25) 3D interface USB RS-232 interface (DB9)
Integrated Cinema Media Processor	DCI 4K 2D up to 60fps* DCI 4K 3D (24 or 30 fps per eye)* DCI High Frame Rates 2K 3D up to 120fps (60fps per eye) JPEG 2000 bit-rates up to 625Mbps Dual-channel color-correction MPEG-2 (4:2:0 and 4:2:2 up to 60fps) 2x Displayport 2x 3G-SDI inputs 1x HDMI 1.4a (up to 4K 2D 24fps, support for BluRay 3D) 16x AES/EBU audio channels (2x RJ45) 8x GPI, 8x GPO (4x RJ45) 2x Gbe for content connectivity & ingest 2x front-accessible USB 3.0 for fast ingest 2x front-accessible USB 2.0 Video watermarking: Civolution NexGuard Audio watermarking: Civolution Closed captioning devices: Support for SMPTE 430-10 * 4K 24fps is standard. For 4K 60 fps / 4K 3D on ICMP upgrade modules a license is required. Newly-built 4K Barco Alchemy projectors have the license standard included.
Geïntegreerde opslag	1.9TB effective storage (RAID-5) / 3x 1TB Hot-swappable 2.5" hard-drives 3.9TB effective storage (RAID-5) / 3x 2TB Hot-swappable 2.5" hard-drives

TECHNISCHE SPECIFICATIES**DP2K-12C**

Barco Web Commander	Projector Dashboard Projector Control Board Show Player/Editor/Scheduler Automation, 3D, Ingest Dynamic DCP playlists & intermission TMS integration Smart Projector Status Via HTML5 web-browsers including iOS & Android tablets Dual projector 3D: passive and active Auro 11.1 decoding
Barco Communicator	Projector installation & configuration Projector update & maintenance
Projectordiagnose	via Integrated Media Server via Communicator control software via SNMP agent
Voedingsvereisten	220V
Afmetingen	558(H) x 694(W) x 1034(D) mm 22.0(H) x 27.3(W) x 40.7(D) inch NB.: min. 5 cm of air inlet spacing required at the bottom of projector
Gewicht	100kg (220lbs)
Omgevingstemperatuur	35°C / 95°F Max.
Luchtuitstroom	240 – 280 cfm (6,8 – 8 m ³ /min)
Opties	3D add-ons Touch screen monitor, inc. Barco Commander & Communicator Pedestal CineCare Web Auro 11.1 license Barco Escape license Live 3D*** ** In testing *** Software roadmap

Last updated: 15 Nov 2022

Technical specifications are subject to change without prior notice. Please check www.barco.com for the latest information.