

# DP2K-17BLP

Smart Laser cinema projector for screens between 13-18m (43-59 ft)



MODULAR

17K

LUMENS

<18m>

SCREEN



LASER PHOSPHOR

- **Reduced total cost of ownership**
- **Unprecedented ease of mind**
- **Superior image quality**

The DP2K-17BLP delivers consistent, razor-sharp, and high-contrast images with 17,000 lumens brightness. It's perfectly suited for mid-size movie screens ranging from 13 up to 18 meters (43 up to 59 feet).

#### **Reduced total cost of ownership**

Eliminating all lamp-related costs, the DP2K-17BLP provides a very attractive TCO. Thanks to its unique cooling system, the projector boasts a 30,000-hour constant brightness at typical usage conditions. Its significantly higher optical efficiency results in electricity bill savings of up to 40%.

#### **Unprecedented ease of mind**

The DP2K-17BLP cuts operating expenses, reduces operational complexity, and optimizes labor cost. The projector increases your uptime and frees you from all lamp-related costs, administration, and maintenance.

#### **Superior image quality**

The DP2K-17BLP offers consistent DCI-compliant image quality, outstanding uniformity, and higher contrast on white and silver screens. Its light output can be dimmed to 30% of the initial brightness, enabling 2D and 3D showings from the same projector.

#### **Retrofit ready**

If you already own a Barco B-series projector you can replace your current lamp house with the unique laser phosphor retrofit module through an easy on-site upgrade.

**TECHNISCHE SPECIFICATIES****DP2K-17BLP**

Helderheid	17,000 lumens (typical)
Native contrastverhouding	2,400:1 (typical)
Primelenzen	1.25-1.90; 1.49-2.06; 1.61-2.31; 1.82-2.86; 2.15-3.6; 2.80-5.50
Resolutie	2,048 x 1,080
Langdurige stabiliteit van helderheid	30,000 hrs @ average usage conditions
Afmetingen (B x L x H)	Projector: 754 x 1,129 x 604 mm / 29.69 x 44.5 x 23.78 inches Cooler: 561.5 x 738.5 x 348 mm / 22.11 x 29.07 x 13.7 inches
Gewicht	Projector: 144kg (318 lb) Cooler: 32kg (70.6 lb)
Lengte koelvoestofslang	4 hoses; 0.5m, 2.5m, 5m, and 8m (1.6ft/8.2ft/16.4ft/26.2 ft)
Verticale scheiding tussen koeler en projector	Maximum 3m (10ft) (higher or lower)
Voedingsvereisten	Projector: single phase 200-240V 15A Cooler: obtains power from the projector
Warmtebelasting (max. vermogen)	7526 BTU/h
Omgevingstemperatuur	35°C (95°F) Max. (projector and cooler)
Omgevingsvochtigheid	85% Max. (projector and cooler)
Energieverbruik	Projector (incl. cooler): 2.4 kW
Mediaserver	Barco Alchemy ICMP and other IMB brands supported.
Geluidsniveau	dB(A) @ 1 m: 67.6 dB(A) 62 dB(A) (half fan speed)
3D-systemen	Active glasses systems and polarization systems on silver screens are supported. Color separation systems (Dolby3D and 6P) are not supported.
Veiligheidsvereisten	Class 1 risk group 3 Show safety: the customer shall take precaution for the laser safety (respect the hazard distance and separation height) according to local laser show safety regulations. Workplace safety: the customer shall take precaution for: <ul style="list-style-type: none"><li>workplace safety as prescribed by the local authorities</li><li>basic laser safety training for operators</li><li>laser safety program implementation in the company;</li><li>access limitation only to trained personnel: area labelling, etc.</li></ul>

Last updated: 24 Feb 2021

Technical specifications are subject to change without prior notice. Please check [www.barco.com](http://www.barco.com) for the latest information.