

FLD+ 0.65 : 1 (EN47)



Focus range 0.5-4.0 m

Throw ratio

- SX+ 0.66:1
- 1080 / WUXGA 0.61:1
- Panorama / WQXGA 0.65:1
- F80: 0.91 : 1 (WQXGA/4K UHD)
(F80 requires the FLD/FLD+ lens adapter and custom third part support is needed)

TECHNISCHE SPECIFICATIES**FLD+ 0.65 : 1 (EN47)**

Effectieve f-getal	F 2.1 Motorized Iris F# 2.1-6.0
Zoomverhouding	No zoom Motorized focus
Brandpuntsafstand	12.6 mm
Focusbereik	Optical Performance 0.5-4.0 m
Aangepast focusbereik	Extended focus range is available, please contact sales for details
Gewicht	5.4 kg
Projectieverhouding	DMD chip <ul style="list-style-type: none">■ WQXGA 0.65:1■ 1080p/WUXGA 0.65:1■ SXGA+ 0.65:1

Image size tolerance +/-5%

Last updated: 16 Dec 2021

Technical specifications are subject to change without prior notice. Please check www.barco.com for the latest information.