

# FLD 3.8 - 6.5 : 1 (EN16)



Focus range: 4.0 - 40.0 m

Throw ratio

- SX+ 4.10-7.10:1
- 1080 / WUXGA 3.80-6.50:1

**TECHNISCHE SPECIFICATIES****FLD 3.8 - 6.5 : 1 (EN16)**

---

Effectieve f-getal	F 2.1-2.66 Motorized Iris F# 2.1-6.5
Zoomverhouding	1.74 Motorized zoom and focus
Brandpuntsafstand	78.3-136.2 mm
Focusbereik	Standard: 4m – 40m
Aangepast focusbereik	Extended focus range is available, please contact sales for details
Gewicht	2.5 kg
Projectieverhouding	DMD chip <ul style="list-style-type: none"><li>■ 1080p /Wuxga 3.8-6.5:1</li><li>■ SXGA+ 4.1-7.1:1</li><li>■ 720p 4.5-7.8.1</li><li>■ XGA 5.6-9.7:1</li></ul>

---

Image size tolerance +/-5%

Last updated: 17 Mar 2022

Technical specifications are subject to change without prior notice. Please check [www.barco.com](http://www.barco.com) for the latest information.