

# UDX-W32

32,000 lumens, WUXGA, 3-chip DLP laser phosphor large venue projector



- **Stunning experiences thanks to high-brightness images**
- **Savings on installation and shipping time**
- **Laser phosphor light source for reduced costs**
- **24/7 operation**

The UDX range delivers stunning experiences and savings on installation and shipping time, reducing costs significantly. The most compact, high-brightness laser projectors with integrated cooling on the market, the UDX projectors bring reliable and razor-sharp 4K images to every type of event and venue.

The UDX-W32 features WUXGA resolution and 32,000 lumens light output to ensure flawless shows with accurate colors at all times. The Constant Light Output (CLO) functionality also guarantees peace of mind by providing constant brightness and color over time. The UDX platform offers the widest color spectrum in the industry. Without compromising on brightness, the UDX color quality matches the renowned Xenon quality and outperforms the Rec. 709 color space.

### **Cut costs with laser projection**

Thanks to their laser phosphor light source, lamp-related costs and maintenance as well as image flicker, belong to the past. The UDX series delivers a long lifetime and high reliability to ensure minimum downtime. The UDX's compact and rugged design allows you to reduce shipping and labor costs. The modular components can be removed quickly to limit servicing time. You can also reuse your TLD+ lenses.

### **Pick your brightness and resolution**

The unique FLEX<sup>2</sup> feature will allow you to tune and lock your brightness and resolution to a specific show. You'll now need less projectors to cover a wider range of brightness levels and resolutions.

### **Faster processing for sharper images**

The Barco Pulse 4K electronics offer an intuitive interface and flexible, user-friendly, embedded control software. Its Single Step Processing (SSP) allows for sharper images and less latency.

**TECHNISCHE SPECIFICATIES****UDX-W32**

Projector type	WUXGA 3-chip DLP digital projector
Technology	0.96" DMD™ x3
Resolution	1,920 x 1,200
Brightness	32,000 center lumens* / 31,000 ansi lumen / 34,000 ISO
Contrast ratio	2,200:1
Brightness uniformity	95%
Aspect ratio	16:10
ScenergiX	Horizontal and vertical edge blending
Lenses	TLD+ 0.37, 0.65-0.85, 0.73:1 ; 1.2:1 ; 0.8-1.16 ; 1.25 -1.6:1 ; 1.5-2.0:1 ; 2.0-2.8:1 ; 2.8-4.5:1 ; 4.5-7.5:1 ; 7.5-11.5:1
Optical lens shift	Vertical between -100% to +130%, depending on lens Horizontal up to +/-40%, depending on lens Motorized zoom and focus (with lens memory on TLD lenses) Motorized lens shift (with position memory on all lenses)
Color correction	P7
Light source	laser phosphor with inorganic phosphor wheel
Light source lifetime	25,000 hrs
Optical dowser	Digital
Picture-by-picture	Two sources simultaneously
Sealed DLP™ core	Standard
Orientation	360°
DMX 512	Standard
WARP	Direct adjust OSD + toolset
Image processing	Embedded warp & blend
Keystone correction	Yes
Integrated web server	Yes
CLO (constant light output)	Standard
3D	Active eye wear (optional), passive circular (optional); 2 flash up to 200Hz*
Inputs	Single HDBaseT; HDMI2.0 (HDCP2.2, HDR10); DP 1.2 (HDCP 1.3); Quad 3G/12G SDI / BarcoLink ULTRA
Optional Inputs	Quad DP1.2 / Fiber SFP

**TECHNISCHE SPECIFICATIES****UDX-W32**

<b>Input resolutions</b>	From NTSC up to 4K (4,096 x 2,160) refresh rates: 24hz to 120hz 4K/4KUHD (4096 x 2160/ 3860 x 2400) to 240hz WQXGA (2560 x 1600)
<b>Max. pixel clock</b>	600 MHz
<b>Software tools</b>	Projector Toolset + Android** app + iOS** app
<b>Control</b>	XLR wired + IR, RS232, Wifi** (opt), GSM** (opt)
<b>Network connection</b>	10/100 base-T, RJ-45 connection, Wifi** (optional)
<b>Power requirements</b>	120-160V (reduced power) / 200-240V (+/-10%), 20A, 50-60Hz
<b>Max. power consumption</b>	2,900 W nom / 3,100 W max. / STBY less than 10 W
<b>Noise level (typical at 25°C/77°F)</b>	52dB(A)
<b>Operational ambient temperature</b>	0-40°C / 32°-104°F
<b>Operational humidity</b>	0-80% (non condens)
<b>Dissipation BTU</b>	Max. 9,895 BTU/h
<b>Dimensions (WxLxH)</b>	660 x 830 x 350 mm / 25.95 x 32.7 x 13.78 inches
<b>Shipping Dimensions</b>	(WxLxH) 800 x 1200 x 685 mm / 31.49 x 47.24 x 26.96 inches
<b>Weight</b>	92kg (202 lbs)/shipping weight from factory: 110kg (242 lbs)
<b>Standard accessories</b>	Power cord, wireless/XLR wired rugged remote control
<b>Certifications</b>	Compliant with UL60950-1 and EN60950-1 complies with FCC rules & regulations, part 15 Class A and CE EN55032 Class A, Rohs
<b>Warranty</b>	3 years
<b>*</b>	+/-10%

Last updated: 17 Jan 2020

Technical specifications are subject to change without prior notice. Please check [www.barco.com](http://www.barco.com) for the latest information.